

Model 388MR

Current Transformer with Multi-Ratio Window Diameter 5.75"

Application

Relaying.

Terminals are brass screws No.10-32 with one flatwasher and lockwasher.

Frequency

50-400 Hz.

Approximate weight 35 lbs



Insulation Level

600 Volt, 10 kV BIL full wave.




Model 388MR


Catalog Number	Relay Class	Continuous Thermal Rating Factor	
		@ 30 °C	@ 55 °C
388-601MR	C100	2.0	2.0
388-122MR	C200	2.0	1.5
388-202MR	C200	1.5	1.33
388-302MR	C400	1.5	1.0
388-402MR	C400	1.33	1.0




Model 388MR




Model 388-122MR




Model 388-402MR



Model 388-202MR



Model 388-302MR



GEGridSolutions.com

Grid-AIS-L4-ITL_Model_388MR-1302-2017_05-EN. General Electric Company and Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

Worldwide Contact Center

Web: www.GEGridSolutions.com/contact

Phone: +44 (0) 1785 250 070

USA and Canada: +1 (0) 800 547 8629

Europe, Middle East and Africa: +34 (0) 94 485 88 00

