

2017-02-08





Specifications

General	
	TDMA, 47 timeslots per second,
structure	7 Payload Bytes per slot

Physical Interface		
DB-25 Connector	3 x RS-232C Serial Ports	
	(1.2 to 115.2 kbps)	
	1 x 10-BASE-T Ethernet Port	
USB Connector	1 x USB Host	
Power	2-pin locking phoenix type	
LEDs	LAN, COM1, COM2, COM3, PWR	

Protocols		
Management	Serial Console, Telnet, SNMP	
File Transfer	TFTP	

Environmental		
Temperature:	-30C - +70C (-22F - +158F)	
Humidity	95% at 40C (104F)	
	non-condensing	
Input Power	10 to 16 VDC 2A Max	

Mechanical		
Case	Die Cast Aluminum	
Mounting Options	Flat surface mount brackets, DIN rail	
Dimensions	1.25 H x 6.75 W x 4.5 D in.	
Weight	2 lbs	

Agency Approvals		
FCC/IC	CFR 47 Part 15	
CSA	Class 1 Div 2	
	Groups A, B, C and D for hazardous	
	locations (ANSI/UL equivalent)	

For additional information, please visit <u>gemds.com</u>

GE MDS reserves the right to make changes to specifications of products described in this data sheet at any time.