

KELMAN MINITRANS

Cost-effective On-line DGA & Moisture for Transformers

Knowledge of the condition of transformers is essential for all electrical networks and on-line monitoring of transformers is an increasingly vital component of successful asset management programs. The information provided by multi-gas on-line DGA allows valuable asset capabilities to be maximized and expensive failures to be avoided.

Dissolved Gas Analysis (DGA) and moisture measurement of the insulation oil are recognized as the most important tests for condition assessment of transformers. Traditionally performed in a laboratory environment, the Kelman™ MINITRANS provides for on-line discrete DGA monitoring of key gases associated with arcing, cellulose degradation and general fault conditions.

Key Benefits

- Cost effective on-line DGA
- Remote insight into transformer condition
- Discrete measurement of 3 key gases: Hydrogen, Carbon Monoxide and Acetylene; plus Moisture
- Faults can be detected in their infancy
- Generic fault type can be classified from results
- Transformer load and output can be optimized safely
- Aids condition based and predictive maintenance strategies
- Available with AC or AC/DC power supply

Applications

The MINITRANS facilitates entry into discrete on-line DGA and moisture monitoring for transformers and other oil insulated filled electrical equipment. The MINITRANS gives insight on developing faults, paper degradation and electrical arcing. It provides trending of gas-in-oil through its close integration with GE Vernova's powerful Perception™ Fleet software suite and/or users own software, historian and SCADA systems.

At a price that facilitates higher volumes of monitor deployment, The MINITRANS can be utilized to monitor any size of transformer, but is most widely employed to expand multi-gas on-line DGA coverage beyond the typical candidates of large, system critical or compromised transformers. It helps asset owners incorporate on-line DGA across a larger portion of their fleet, with a view to extending asset life, preventing unexpected failure and operating on a condition based/predictive maintenance schedule.

- Auxiliary GSU transformers
- Renewable Transformers
- Transmission transformers
- Distribution transformers



Cutting Edge Technology

- Three key fault gases plus moisture
- Automated headspace gas extraction
- State of the art photo-acoustic spectroscopy
- (PAS) measurement technology
- No carrier or calibration gases required
- Sampling frequency up to once per hour

Ease of Use

- Easy installation: no outages required reducing expense and inconvenience for user
- No consumables and minimal maintenance reduces running costs and site visits
- Extensive local and remote communications options available
- Sampling frequency user-configurable, versatile and flexible
- LCD display provides up to date information

Configurable Alerts

- Two sunlight visible front panel LED arrays
- User configurable relay contacts
- Alarms can be set or changed locally or remotely using Perception software
- Caution and alarm modes can be used to automatically increase sampling frequency

Integrated Solution

- Integrated load monitoring allows DGA analysis against transformer loading
- Can be connected to GE Vernova's Perception software for sophisticated graphical trending & diagnostic tools



GE VERNOVA

Perception Fleet Software

Easy to install and configure, GE Vernova's Perception™ Fleet Asset Management Software is the ideal companion to your GE Vernova on-line monitors for both transformers and circuit breakers.

Perception Fleet moves customers from a manual, one-on-one asset assessment process to an automated and continuous fleet management solution.

Perception Fleet automatically downloads data from each GE Vernova online monitor and populates its database. It provides asset experts with comprehensive transformer diagnostic tools and data trending capabilities, as well as providing asset managers with asset fleet ranking based on health and risk indexes.




Technical Specifications

MEASUREMENTS	
Range (LDL - UDL)	
Hydrogen (H ₂)	5 - 5,000 ppm
Carbon Monoxide (CO)	10 - 50,000 ppm
Acetylene (C ₂ H ₂)	3 - 50,000 ppm
Moisture (H ₂ O)	0-100% RS (given in ppm)
Accuracy*	±10% or ±LDL (whichever is greater)
*Accuracy quoted is the accuracy of the detectors during calibration.	
Frequency	
Variable - once per hour to once every 4 weeks	
Technology	
Uses photo-acoustic spectroscopy (PAS) to give highly reliable results. Field proven with over 10,000 Kelman PAS systems deployed in over ninety countries worldwide	
Fully embedded processor and internal data storage for 10,000 records - over eight years of data at default sampling rate - protected by non-volatile memory	
FEATURES	
Alarms	
Two sunlight visible front panel LED arrays (Red & Green)	
Single Pole Alarm Relays, NO and NC provided: 1A@250Vac, 200mA@125Vdc, 150mA@300Vdc, 1A@30Vdc	
Six alarm setting screens or scenarios are available, which can set alarms based on the level of the three gasses/moisture, and rates of change for each gas	
Each alarm setting screen can activate the alarm relays or send an SMS message if equipped with the optional cellular modem	
All alarms can be set or changed locally or remotely using Perception software	
Caution and alarm modes can be used to increase sampling frequency	
Communications	
Two separate channels for remote communications, local USB connection and Ethernet connection	
Communications protocols supported include MODBUS®, MODBUS/TCP, DNP3.0, IEC®61850	
Modules available for communication via RS232, RS485, Ethernet, Fiber Optic, PSTN and cellular GSM/GPRS modems	

ENVIRONMENT	
Conditions	
Operating Ambient Temperature	-35 °C to +55 °C (-40 °F to +131 °F): AC version -17 °C to +55 °C (1 °F to +131 °F): AC/DC version
Operating Ambient Humidity	0-95 % RH, non-condensing
Oil Temperature at Valve**	-10 °C to +100 °C (14 °F to +212 °F)
**Based on testing carried out using VOLTESSO™ 35 mineral oil, over a ¼" pipe run of 10 metres or less from oil supply or return valve to monitor connection point and on transformer oil supply valve volumes of 200 ml or less. For oil temperatures colder than -10 °C GE Vernova recommend the use of heat trace cabling on piping	
Enclosure Rating	
IP55 certified	
304 Stainless Steel (316 option)	
Power Requirements	
Available with either AC or AC/DC power supply	
AC Version ***	Nom: 115/230 Vac, Range: 103-126/207-253 Vac, 47-63 Hz, 6A max
AC/DC version	Nom: 100-230 Vac, Range: 90-253 Vac, 45-65Hz, 5A max Nom: 100-220 Vdc, Range: 90-242 Vdc, 5A max
***AC input auto-switching	
Mechanical	
Dimensions	600 mm x 380 mm x 350 mm 24 " x 15 " x 14 "
Weight	Installed weight 31Kg (68lb) Shipping weight 49Kg (108lb)

Grid Solutions
Lissue Industrial Estate East
Unit 1, 7 Lissue Walk
Lisburn BT28 2LU
United Kingdom
Tel: +44 (0) 2892 622915

For more information visit
governova.com/grid-solutions



Kelman, MINITRANS and Perception are trademarks of the General Electric Company.

Modbus is a registered trademark of Schneider Automation Inc., IEC is a registered trademark of Commission Electrotechnique Internationale. Voltesso is a registered trademark of Exxon Mobil Corporation. Kelman, DS-Agile and Perception are trademarks of the General Electric Company.

GE Vernova reserves the right to make changes to specifications of products described at any time without notice and without obligation to notify any person of such changes.

© 2026 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-17281-(E)
English
260603