GE Grid Solutions

F35

Gas-Insulated Substations 72.5 kV, 31.5 kA, 2 500 A

GE makes the most of 50 years of experience in design, material selection, development, engineering, manufacturing and servicing of gas-insulated substations.

GE's F35 GIS meet the challenges of networks up to 72.5 kV for all applications: power generation, transmission, distribution, tertiary and industry.

High Availability

- Extensive experience and reliability with more than 4,500 bays installed in 67 countries
- Current transformers outside gas
- Pure-spring circuit-breaker drives

Short Site Works

- Up to 3 bays assembled together, wired, tested and shipped to site
- Simple on-site testing thanks to disconnecting function of voltage transformer and surge arrester

Operational Safety

• Drives and accessories within easy reach

Modular and Versatile

- Applicable in wind farms, urban and industrial substations
- High modularity enables complex layouts in a compact arrangement



Lowest Cost of Land and Civil Works

- Bay volume reduced by
 - 23% compared to previous design
 - 40% compared to 145 kV
- Compact GIS bay width of only 0.68 m

Smart Grid Features


• Full-digital monitoring, control and protection

Low Environmental Impact

- First-in-class sealing system
- Gas monitoring system BWatch
- Designed for g³ application



F35 - 72.5 kV, 31.5 kA, 2 500 A - Single busbar diagram







Bay width: 680 mm

Also available:

- Other single-line diagrams
- Stand-alone control cubicles
- Specific layouts





Ratings

General		
Reference electrotechnical standards		IEC / IEEE
Voltage	kV	72.5
Withstand voltages		
Short-duration power-frequency, phase-to-earth / across isolating distance	kV	140 / 160
Lightning impulse, phase-to-earth / across isolating distance	kVp	325 / 375
Frequency	Hz	50 / 60
Continuous current	А	up to 2500
Short-time withstand current	kA	31.5
Peak withstand current	kAp	85
Duration of short-circuit	S	3
Installation		indoor/ outdoor
Ambient temperature range	°C	down to -30 / up to +55
Circuit-Breaker		
First-pole-to-clear factor		1.5
Short-circuit breaking current	kA	31.5
Short-circuit making current	kAp	85
Operating sequence		O – 0.3 s – CO – 3 min – CO / CO – 15 s – CO
Drive type (three-phase or single-phase)		pure-spring
Breaking time	ms	50
Closing time	ms	70
Mechanical endurance	class	M2
Capacitive switching	class	C2
Disconnector and Low-Speed Earthing Switch		
Capacitive current switching	А	0.1
Bus-transfer current switching capability	A/V	1600 / 10
Mechanical endurance	class	M2
Make-Proof Earthing Switch		
Making current capability	kAp	85
Switching capability - electromagnetic coupling	A / kV	80 / 2
Switching capability - electrostatic coupling	A / kV	2 / 6
Mechanical endurance	class	M1
Other data available on request		

Other data available on request.

For more information please contact GE Grid Solutions

Worldwide Contact Center

Web: www.GEGridSolutions.com/contact Phone: +44 (0) 1785 250 070

GEGridSolutions.com

IEC is a registered trademark of Commission Electrotechnique Internationale.

GE and the GE monogram are trademarks of General Electric Company.

GE reserves the right to make changes to specifications of products described at any time without notice and without obligation to notify any person of such changes.

F35-72kV-Brochure-EN-2019-04-Grid-GIS-1654. © Copyright 2019, General Electric Company. All Rights Reserved.

