GE Grid Solutions

F35

Gas-Insulated Substations 170 kV, 50 kA, 4 000 A

GE makes the most of 50 years of experience in design, material selection, development, engineering, manufacturing and servicing of gas-insulated substations.

GE's F35 GIS meet the challenges of networks up to 170 kV for all applications: power generation, transmission, distribution, tertiary and heavy industry.

Highest Availability

- Best experience and reliability data
- Current transformers outside SF₆
- Drives and accessories at easy reach
- Pure-spring circuit-breaker drives

Shortest Site Works

- Complete bays assembled, wired, tested and shipped
- Isolating device for voltage transformer / surge arrester



Lowest Cost of Land and Civil Works

• The most compact 170 kV GIS: bay footprint 30 % below market average

Smart Grid Features

• Full-digital monitoring, control and protection

Environment Friendliness


• First-in-class SF₆ sealing system


Customer Benefits


- Maximum safety
- Compact but accessible
- Field-proven reliability
- First-class availability
- Low total cost of ownership
- Smart Grid ready
- Low environmental impact



F35 - 170 kV, 50 kA, 4 000 A - Double busbar diagram








Bay width: 1 000 mm


Also available:

- Other single-line diagrams
- Standalone control cubicles
- Specific layouts



800 1400 mini 4133 mini 600

Line bay



Bus coupler bay

Ratings

General		
Reference electrotechnical standards		IEC / IEEE
Voltage	kV	170
Withstand voltages		
Short-duration power-frequency, phase-to-earth / across isolating distance	kV	325 / 375
Lightning impulse, phase-to-earth / across isolating distance	k∨p	750 / 860
Frequency	Hz	50 / 60
Continuous current	Α	up to 4000
Short-time withstand current	kA	50
Peak withstand current	kAp	125 / 130
Duration of short-circuit	S	3
Installation		indoor
Ambient temperature range	°C	down to -25 / up to +55
Circuit-Breaker		
First-pole-to-clear factor		1.5
Short-circuit breaking current	kA	50
Short-circuit making current	kAp	125 / 130
Operating sequence		0 - 0.3 s - C0 - 3 min - C0 / C0 - 15 s - C0
Drive type (three-phase or single-phase)		pure-spring
Breaking time	ms	50
Closing time	ms	100
Mechanical endurance	class	M2
Capacitive switching	class	C2
Disconnector and Low-Speed Earthing Switch		
Capacitive current switching	А	0.1
Bus-transfer current switching capability	A/V	1600 / 10
Mechanical endurance	class	M2
Make-Proof Earthing Switch		
Making current capability	kAp	125 / 130
Switching capability - electromagnetic coupling	A / kV	80 / 2
Switching capability - electrostatic coupling	A/kV	3/9
Mechanical endurance	class	M1
Other data qualitable on request	000	

Other data available on request.

For more information please contact GE Grid Solutions

Worldwide Contact Center

Web: www.GEGridSolutions.com/contact Phone: +44 (0) 1785 250 070

GEGridSolutions.com

 ${\sf IEC} \ is \ a \ registered \ trademark \ of \ Commission \ Electrotechnique \ Internationale.$

GE, the GE monogram, $g^{\scriptscriptstyle 3}$ and $g^{\scriptscriptstyle 3}$ logo are trademarks of General Electric Company.

GE reserves the right to make changes to specifications of products described at any time without notice and without obligation to notify any person of such changes.

Grid-GIS-L3-F35_170_kV-0170-2016_09-EN \otimes Copyright 2016, General Electric Company. All Rights Reserved.

