

Kelman TRANSFIX

Extensive on-line DGA & moisture

Dissolved Gas Analysis (DGA) and moisture measurement of the insulating oil are recognized as the most important tests for the condition assessment of transformers. Multi-gas DGA has traditionally been confined to the laboratory environment and infrequent off-line manual sampling, forming part of time based maintenance strategies. As the average age of transformers globally continues to rise, the possibility of rapid ageing, unplanned outages and even catastrophic failure between off-line tests also increases, leading many asset owners to adopt on-line DGA monitoring of equipment to increase network reliability.

The Kelman™ TRANSFIX offers discrete multigas on-line DGA and moisture monitoring for transformers. Utilizing photo-acoustic spectroscopy (PAS) measurement technology, which is well suited to field application, it provides laboratory challenging levels of precision and repeatability. Full 9 gas oil sampling and analysis can be performed as often as every hour.

Through close integration with GE's powerful Perception™ software suite and/or user's own software, historian and SCADA systems, the TRANSFIX offers full gas-in-oil trending, analysis and diagnostic capabilities including various diagnostic methods prescribed by international standards.

Key Benefits

- Remote insight into transformer condition enables rapid action to correct any issue detected
- Discrete measurement of all fault gases facilitates full remote diagnostic without having to go to site and take an oil sample
- Faults can be detected in their infancy and outage scheduled when less inconvenient and less costly (normal working hours)
- Aids condition based and predictive maintenance strategies
- Compatible with mineral insulating oils or ester based oils (natural and synthetic)

Applications

Knowledge of the condition of transformers is essential for all electrical networks and on-line monitoring of transformers is an increasingly vital component of successful asset management programs. The information provided by multi-gas on-line DGA allows valuable asset capabilities to be maximized and expensive failures to be avoided.

Capable of monitoring all sizes of transformers, TRANSFIX is most widely employed for monitoring large, system critical or already compromised transformers with a view to extending asset life, preventing unexpected failure and operating on a condition based maintenance schedule. Some examples include:

- GSU transformers
- HVDC station transformers
- Transmission transformers
- Mission critical industrial transformer



Cutting Edge Technology

- Nine gases plus moisture in a single monitor
- Automated headspace gas extraction and state of the art photo-acoustic spectroscopy (PAS) measurement technology
- No carrier or calibration gases required
- Long service life with minimal maintenance

Ease of Use

- Easy installation: no outages required reducing expense and inconvenience for user
- No consumables and minimal maintenance reduces running costs and site visits
- Extensive remote communications options and protocols available (including IEC® 61850)
- Sampling frequency is user-configurable, up to once per hour
- Can be connected to normal AC power or protected DC supply
- Supports new lower flammability ester based oils as well as mineral insulation oils

Configurable Alerts

- Two alarm levels (one for Caution and one for Alarm) can be set to show increasing severity
- Sunlight visible front panel LED arrays
- Six user configurable alarm relay contacts
- Caution and alarm modes can be used to automatically increase sampling frequency

Integrated Solution

- Partners Intellix™ MO 150 and BMT 300 products and combines well with some of the GE Industrial Communication products
- Can be configured by and data downloaded to GE's Perception software which provides graphical gas level trending and diagnostic methods based on International standards
- Also integrates to Perception Fleet to provide health/risk ranking of the monitored transformers compared to other fleet assets




Perception Software


TRANSFIX comes as standard with Perception Desktop to help you configure the unit but also download the stored data in order to view gas level trends and analyse the data using diagnostic methods based on International standards.

For asset managers with a large number of monitored transformers, Perception Fleet takes it one step further and automatically performs the data analysis to assign a health/risk index to every transformer in your fleet. It then ranks all assets to give an overview of your transformers' condition/risk and highlight the worst ones requiring urgent attention or replacement.

Perception Fleet further offers customisable overview reports, wallboard fleet visualization, alarm email notification and data import and export facility. The notification and support for smart phone/tablet connection ensures that the right person can access critical data easily should a transformers condition change.



Transformer overview report



IEEE® C57.104 DGA diagnostic



Transformer health/risk overview

Technical Specifications

MEASUREMENTS

Technology

Uses photo-acoustic spectroscopy (PAS) for field proven highly repeatable results

Eight target gases plus Total Dissolved Combustible Gas (TDCG) value. Estimation of Nitrogen content for free breathing transformers

Suitable for transformers using mineral insulating oil and also ester based oils (natural or synthetic)

Range (LDL - UDL)

Hydrogen (H₂)	5 - 5,000 ppm
Carbon Monoxide (CO)	2 - 50,000 ppm
Carbon Dioxide (CO₂)	20 - 50,000 ppm
Methane (CH₄)	2 - 50,000 ppm
Acetylene (C₂H₂)	0.5 - 50,000 ppm
Ethane (C₂H₆)	2 - 50,000 ppm
Ethylene (C₂H₄)	2 - 50,000 ppm
Oxygen (O₂)	100 - 50,000 ppm
Nitrogen (N₂) *	10,000 - 100,000 ppm
Moisture (H₂O)	0 - 100% RS (given in ppm)

Accuracy **

Oxygen (O₂)	±10%
Nitrogen (N₂)	±15%
All other gases	±5% or ±LDL (whichever is greater)
Moisture (H₂O)	±3%

*N₂ available on free-breathing transformers only.

**Accuracy quoted is the accuracy of the detectors during calibration. Gas -in oil measurement accuracy may also be affected by sampling and/or oil type.

Frequency

Configurable from once per hour to once every 4 weeks. Factory default; every eight hours

Faster sampling automatically triggered upon caution alarm level reached

FEATURES

Display

4x sunlight visible LED arrays
 Internal backlit LCD, 4 lines x 20 characters

Communication

Two separate channels for remote communications plus local USB connection

Ethernet connection (RJ45) on one channel using Modbus® is standard

Communication protocols supported include Modbus, DNP3.0, IEC 61850

Modules available for communication via RS485, Ethernet, Fiber optic, PSTN and cellular GSM/GPRS modems

8 channel configurable analogue output, 4-20mA, available as an option

Alarms

Two sunlight visible front panel LED arrays (Red & Yellow)

All alarms can be set or changed locally or remotely using Perception software

Six alarm setting scenarios are available for setting alarms based on the level of any of the nine gases, TDCG and moisture, and rates of change for each gas

Each alarm setting scenario can activate one of six alarm relays, the red or yellow front panel indicator or send an SMS message if equipped with the optional cellular GSM modem

Six dry contact alarm relays (type C, SPDT), NO/NC, 3A@250Vac, 3A@30Vdc, 200mA@125Vdc, 150mA@300Vdc,

Caution mode and alarm mode can be used to increase sampling frequency

Others

Internal data storage for 10,000 records - over ten years of data at default sampling rates

Non-volatile memory storage to prevent loss of data

Supplied load CT allows to perform DGA analysis against transformer load

ENVIRONMENT

Conditions

Operating ambient temperature	-40 °C to +55 °C (-40 °F to +131 °F) AC version -17 °C to +55 °C (0 °F to +131 °F) AC/DC version
Operating ambient humidity	0-95 % RH, non-condensing
Oil temperature at valve***	-20 °C to +120 °C (-4 °F to +248 °F)

***Based on testing carried out using Voltesso® 35 mineral oil, over a ¼ " pipe run of 10 metres or less from oil supply or return valve to monitor connection point and on transformer oil supply valve volumes of 200ml or less. For oil temperatures colder than -20 °C, GE recommends the use of heat trace cabling on piping

Enclosure Rating

IP55 certified

304 Stainless Steel (316 SS option)

Power Requirements

Available with either AC or AC/DC power supply

AC Version

Nom: 115-230 Vac, Range: 103-126/207-253 Vac, 47-63 Hz, 8A max

AC/DC version

Nom: 100-230 Vac, Range: 90-253 Vac, 45-65Hz, 5A max
 Nom: 100-220 Vdc, Range: 90-242 Vdc, 5A max

Mechanical

Dimensions

800 mm x 600 mm x 389 mm
 31.5 " x 23.6 " x 15.3 "

Weight

Installed weight 72 Kg (159 lb)
 Shipping weight 110 Kg (243 lb)

OPTIONS

Mounting stand

Cradle mount (for mounting on transformer)

Sun canopy

Inputs to connect other analogue sensors (e.g. top and bottom oil temperature)

Option for monitoring fibre optic probes already embedded inside the transformer windings

GE Grid Solutions
 Lissie Industrial Estate East
 Unit 1, 7 Lissie Walk
 Lisburn BT28 2LU
 United Kingdom
 Tel: +44 (0) 2892 622915

GEGridSolutions.com

GE, the GE monogram, Kelman, Intellix and Perception are trademarks of the General Electric Company.

Modbus is a registered trademark of Schneider Automation, Inc. IEC is a registered trademark of Commission Electrotechnique Internationale. Voltesso is a registered trademark of Exxon Mobil Corporation. IEEE is a registered trademark of the Institute of Electrical and Electronics Engineers Inc.

GE reserves the right to make changes to specifications of products described at any time without notice and without obligation to notify any person of such changes.

Copyright 2020, General Electric Company. All Rights Reserved.

GEA-17280D(E)
 English
 200908

