

GE

Energy Connections

Model 570

Current Transformer
Window Size 3.56" x 0.79"

Application

Metering.

Frequency

50-400 Hz.

Insulation Level

600 Volts, 10 kV BIL full wave.

Continuous Thermal Current Rating Factor

1.33 at 30 °C. amb.,
 1.0 at 55 °C. amb.

Terminals are brass studs No. 10-32
 with one flatwasher, lockwasher and
 regular nut.

Approximate weight 3 lbs.



REGULATORY AGENCY APPROVALS





Manufactured to meet the requirements of ANSI/IEEE C57.13.
 Classified by U.L. in accordance with IEC 44-1

Model 570

Catalog Number	Current Ratio	ANSI Metering Class at 60 Hz					Secondary Winding Resistance (Ω @ 75 °C)
		BO.1	BO.2	BO.5	BO.9	B1.8	
570-201	200:5	1.2	2.4	—	—	—	0.042
570-251	250:5	1.2	1.2	2.4	—	—	0.053
570-301	300:5	0.6	1.2	1.2	2.4	—	0.063
570-401	400:5	0.6	0.6	1.2	2.4	2.4	0.084
570-501	500:5	0.3	0.6	1.2	1.2	2.4	0.106
570-601	600:5	0.3	0.3	0.6	1.2	1.2	0.127
570-751	750:5	0.3	0.3	0.6	0.6	1.2	0.158
570-801	800:5	0.3	0.3	0.6	0.6	1.2	0.169
570-102	1,000:5	0.3	0.3	0.3	0.6	0.6	0.211



Model 570



GEGridSolutions.com

Grid-AIS-L4-ITL_Model_570-1329-2017_06-EN. © Copyright 2017. General Electric Company and Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

Worldwide Contact Center

Web: www.GEGridSolutions.com/contact

Phone: +44 (0) 1785 250 070

USA and Canada: +1 (0) 800 547 8629

Europe, Middle East and Africa: +34 (0) 94 485 88 00

