

# KELMAN DGA 900

## Next Generation On-line Multi-gas DGA

Dissolved Gas Analysis (DGA) and moisture measurement of insulating fluids are recognized as the most important tests for condition assessment of transformers. In previous years, multi-gas DGA was traditionally confined to a laboratory environment, with infrequent off-line manual sampling forming part of time-based maintenance strategies. However, as the global average age of transformers continued to rise, the possibility of rapid ageing, unplanned outages and even catastrophic failure between off-line tests also increased, leading many asset owners to adopt on-line DGA monitoring strategies to increase network reliability.

In the early 2000's, GE Vernova's Kelman™ range of analysers brought consumable-free on-line multi-gas DGA to the market and GE Vernova is now proud to introduce the Kelman DGA 900, our next generation multi-gas on-line DGA and moisture analyser. At its heart lies an evolved implementation of GE Vernova's proven Photo-Acoustic Spectroscopy (PAS) measurement technology, providing laboratory challenging levels of precision and repeatability with no consumables and no need for frequent re-calibration. Benefiting from over 40 years of global DGA vendor experience, the Kelman DGA 900 encapsulates learnings and improvements derived from its predecessors to bring improved performance, innovative new features, enhanced user experience and increased robustness.

### Key Benefits

- Provides remote alert and multi-gas diagnostic of deteriorating transformer condition
- Expedites operational decisions without needing to go to site for manual oil sampling
- Issues can be detected in their infancy, avoiding unexpected failures and facilitating planned outages
- Anchors condition based maintenance and asset replacement strategies on hard data
- No need for consumables or frequent recalibration to operate at optimum performance
- New "Rapid Mode" provides near real-time insight on fast developing faults
- Enhanced computing power and scalable I/Os for a flexible transformer monitoring solution
- Compatible with mineral insulating oils and newer ester based fluids (natural and synthetic)



### Proven Technology

- 4th generation of GE Vernova's PAS technology delivering improved accuracy with lower detection limits
- From the only vendor with 15 years PAS experience and installed base of >13,000 units
- No carrier or calibration gas consumables
- Laboratory challenging field measurement of nine gases plus moisture
- Complete DGA analysis up to once per hour and new "Rapid Mode" for critical gases in ~30 min.

### Reliable and Available

- First Kelman device designed by GE Vernova leveraging our quality and continuous improvement ethos
- Enhanced reliability and easier field servicing
- 5-year warranty as standard †
- Factory calibration benchmarked against industry standard laboratory assessment

### Intuitive and Flexible

- Integrated 7" colour LCD screen for simplified local user interaction and visualisation of data
- Lightweight innovative two-enclosure design enables adjacent or separated installation
- Can connect to AC or sub-station DC power

### Scalable and Connected

- Expandable analogue/digital I/Os
- Future proof computing platform ready for feature enhancements
- Designed for cyber security, with a range of comms options and protocols



GE VERNOVA

## Applications

The Kelman DGA 900 is an invaluable foundational tool for implementing Asset Performance Management (APM) across electrical generation, transmission and industry, enabling a condition based asset replacement strategy and delivering improvements in system reliability and availability.

A DS-Agile™ and Grid APM ready device, the DGA 900's wide range of communication methods and protocols enables connection to those platforms and integration with GE Vernova's Perception™ transformer fleet management software as well as other software, historian and SCADA systems.

## Technical Specifications

MEASUREMENTS					
Technology			Frequency		
Automated head-space gas extraction. Photo-acoustic spectroscopy (PAS) gas measurement. Thin film capacitive moisture sensor. Immersed fiber optic oxygen sensor.			Configurable from once per hour to once every 4 weeks. Faster sampling automatically triggered upon alert level reached. “Rapid Mode” provides a rapid indication of the evolution of the gasses indicated below in ~30 minutes.		
Range					
	LDL	UDL	Accuracy*	Repeatability	Available in Rapid Mode
Hydrogen (H <sub>2</sub> )	5	5,000 ppm	± LDL or ±5 %	< 3 %	•
Carb. Monox. (CO)	1	50,000 ppm	± LDL or ±3 %	< 2 %	•
Methane (CH <sub>4</sub> )	2	50,000 ppm	± LDL or ±3 %	< 2 %	•
Acetylene (C <sub>2</sub> H <sub>2</sub> )	0.5	50,000 ppm	± LDL or ±3 %	< 2 %	•
Ethylene (C <sub>2</sub> H <sub>4</sub> )	1	50,000 ppm	± LDL or ±3 %	< 2 %	•
Carb. Diox. (CO <sub>2</sub> )	20	50,000 ppm	± LDL or ±3 %	< 3 %	•
Ethane (C <sub>2</sub> H <sub>6</sub> )	1	50,000 ppm	± LDL or ±3 %	< 2 %	•
Oxygen (O <sub>2</sub> )	100	50,000 ppm	± LDL or ±5 %	< 2 %	•
Nitrogen (N <sub>2</sub> )**	10,000	100,000 ppm	± LDL or ±15 %	< 2 %	•
Moisture (H <sub>2</sub> O)	0	100% RS (in ppm)	± 3% ppm	< 3 %	•

\* Whichever is greater. Accuracy quoted is the accuracy of the detectors during calibration. Gas-in-oil measurement may be affected by oil type and condition. Repeatability as measured from final production test data.


\*\* N<sub>2</sub> value is calculated and available on free-breathing transformers only.

Time Response (typical): 1 measurement cycle ; >95 %: C<sub>2</sub>H<sub>2</sub>, CO, C<sub>2</sub>H<sub>6</sub>, C<sub>2</sub>H<sub>4</sub>, CH<sub>4</sub>, CO<sub>2</sub> ; >90 %: H<sub>2</sub>

FEATURES	
Display	
4 x sunlight visible LED arrays Integrated backlit 7" inch color resistive touch screen (800 × 480) Embedded secure webserver (https)	
Analogue Inputs	
1 x CT input standard 5 x optional analogue inputs slots (Add up to 5 additional load CT's or PT100 inputs or 4-20mA sensor cards)	
Digital Output	
6 x Standard customer programmable dry contact relays (type C, SPDT), NO/NC, 10A @250Vac resistive load, 8A @30Vdc resistive load 1 x standard service alarm relay 1 x standard watchdog relay	

† Terms and conditions apply

FEATURES	
Digital Communications / Protocols	
1 x Modbus® over RS485/TCP/IP as standard 1 x Standard 1Gb Ethernet (RJ45) Option: DNP3.0 over RS485 or TCP/IP Option: IEC 61850 Edition 2 Option: ST/SC Multi-mode fiber converters Option: GPRS/UMTS/HSPA+ modem Option: Wi-Fi (802.11b/g/n)	
Alarms	
Multiple Alarm setting/scenarios, all assignable to relays or SMS Gas: absolute gas level, Rate of Change (ROC), moisture level, Total Dissolved Combustible Gas (TDCG) and 7 x user defined gas ratios alarms Analog inputs: absolute Level, and Rate of Change (ROC) Digital inputs: status transition	



DGA 900 gas levels displayed on the local LCD screen

ENVIRONMENT	
Conditions	
Operating ambient temperature	-40 °C to +55 °C (-40 °F to +131 °F)
Operating ambient humidity	0-95 % RH, non-condensing
Oil temperature at valve***	-20 °C to +120 °C (-4 °F to +248 °F)
***Based on testing carried out using VOLTESSO™ 35 mineral oil, over a ¼" pipe run of 10 metres or less from oil supply or return valve to monitor connection point and on transformer oil supply valve volumes of 200 ml or less. For oil temperatures colder than -20 °C GE Vernova recommends the use of heat trace cabling on piping	

Enclosure		
IP56 certified		
Standard: Powder coated marine grade aluminium (RAL9002)		
Option: Unpainted 316 Stainless Steel		
Power Requirements		
AC	Nominal 100-240 Vac, Range 85-264 Vac, 4A	
DC	Nominal 100-250 Vdc, Range 90-300 Vdc	
Mechanical		
	Analysis Unit	Hub Unit
Dimensions	600 × 484 x	600 × 380
	330 mm	x 330 mm
	23.6 × 19.1 x	23.6 × 15.0
	13.0 in	x 13.0 in
Weight	33.4 Kg	18.5 Kg
	73.6 lb	40.8 lb

OPTIONS	
Mounting stand Sun canopy Longer umbilical cable between units Analogue output of gas values	

## Why GE Vernova as your partner of choice?

### Experience

- Stable, large multinational, here for the long term
- Significant R&D capability to continually innovate and solve any issue
- One-stop shop with largest portfolio of M&D products, software and services
- Focused on product reliability, offering some of the industry's longest warranty periods
- Dedicated regional sales, installation and service teams around the globe
- Largest DGA monitoring installed base: over 50,000 units sold world wide
- Well integrated with GE Vernova's Protection & Control and Industrial Communication products

### Delivering Outcomes



### Support Services

- Installation and commissioning
- Technical support and product training
- Long term maintenance and service agreement
- Product rental solutions

### Expert Services

- Cloud based remote monitoring
- Data diagnostics and interpretation
- Alarm setting and result analysis training

For more information, visit  
**[gevernova.com/grid-solutions](https://gevernova.com/grid-solutions)**

Modbus is a registered trademark of Schneider Automation Inc., IEC is a registered trademark of Commission Electrotechnique Internationale. Voltesso is a registered trademark of Exxon Mobil Corporation. Kelman, DS-Agile and Perception are trademarks of the General Electric Company.

GE reserves the right to make changes to specifications of products described at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



**GE VERNOVA**

GEA-N50032  
English  
251017