

MODEL 100

Current Transformer

Window Diameter 4.00"



REGULATORY AGENCY APPROVALS
 E93779  LR89403
 Manufactured to meet the requirements of ANSI/IEEE C57.13.
 Classified by U.L. in accordance with IEC 44-1

Application

Relay and Metering.

Frequency

50-400 Hz.

Insulation Level

600 Volt, 10 kV BIL full wave.

Terminal are brass studs No. 8-32 with one flatwasher, lockwasher and regular nut.

Order mounting bracket kit 0221B00185 separately.

Multi-ratios available upon request.

Approximate weight 9.5 lbs.

Data Table: Model 100

CATALOG NUMBER	CURRENT RATIO	V.A. ±1% CLASS	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75°C)	CONTINUOUS THERMAL RATING FACTOR	
			B0.1	B0.2	B0.5	B0.9	B1.8		@ 30°C	@ 55°C
100-201	200:5	C10	0.6	0.6	1.2	2.4	—	0.057	2.0	2.0
100-301	300:5 *	C10	0.3	0.3	0.6	1.2	—	0.091	2.0	2.0
100-401	400:5*	C20	0.3	0.3	0.6	0.6	1.2	0.133	2.0	2.0
100-501	500:5*	C20	0.3	0.3	0.6	0.6	1.2	0.166	2.0	1.5
100-601	600:5*	C20	0.3	0.3	0.3	0.6	0.6	0.199	2.0	1.5
100-801	800:5*	C20	0.3	0.3	0.3	0.3	0.6	0.266	1.5	1.33
100-102	1,000:5*	C50	0.3	0.3	0.3	0.3	0.3	0.332	1.5	1.0
100-122	1,200:5*	C20	0.3	0.3	0.3	0.3	0.3	0.374	1.5	1.0
100-152	1,500:5*	C20	0.3	0.3	0.3	0.3	0.3	0.468	1.33	1.0
100-162	1,600:5*	C50	0.3	0.3	0.3	0.3	0.3	0.499	1.33	1.0
100-202	2,000:5*	C50	0.3	0.3	0.3	0.3	0.3	0.624	1.0	0.8
100-252	2,500:5*	C50	0.3	0.3	0.3	0.3	0.3	0.735	1.0	0.8
100-302	3,000:5*	C50	0.3	0.3	0.3	0.3	0.3	0.882	1.0	0.8



Approved for revenue metering by Industry Canada No. T-153



GE VERNOVA



Model 100



For more information, visit
gevernova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50312
 English
 251013