

MODEL 135

Current Transformer

Window Diameter 5.75"



Applications

Relaying and metering.

Frequency

50-400 Hz.

Insulation Level

600 Volts, 10 kV BIL full wave.

Terminals are brass screws No. 10-32 with one flatwasher and lockwasher.

Multi-ratios available on request.

Order mounting bracket kit 0221B00186 separately.

Approximate weight 18 lbs.



Model 135

CATALOG NUMBER	CURRENT RATIO	RELAY CLASS	ANSI METERING AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75°C)	CONTINUOUS THERMAL RATING FACTOR	
			B0.1	B0.2	B0.5	B0.9	B1.8		@ 30°C	@ 55°C
135-500	50:5	-	4.8	-	-	-	-	0.015	2.0	2.0
135-750	75:5	-	2.4	4.8	-	-	-	0.027	2.0	2.0
135-101	100:5	-	1.2	2.4	4.8	-	-	0.036	2.0	2.0
135-151	150:5	C10	0.6	1.4	2.4	4.8	-	0.059	2.0	2.0
135-201	200:5*	C10	0.6	0.6	1.2	2.4	4.8	0.078	2.0	2.0
135-251	250:5*	C20	0.6	0.6	1.2	2.4	2.4	0.113	2.0	2.0
135-301	300:5*	C20	0.3	0.3	0.6	1.2	2.4	0.117	2.0	2.0
135-401	400:5*	C20	0.3	0.3	0.3	0.6	1.2	0.156	2.0	2.0
135-501	500:5*	C50	0.3	0.3	0.3	0.3	0.6	0.181	2.0	2.0
135-601	600:5*	C50	0.3	0.3	0.3	0.3	0.6	0.217	2.0	2.0
135-751	750:5*	C50	0.3	0.3	0.3	0.3	0.6	0.339	2.0	1.5
135-801	800:5*	C50	0.3	0.3	0.3	0.3	0.6	0.362	2.0	1.5
135-102	1,000:5*	C100	0.3	0.3	0.3	0.3	0.3	0.452	1.5	1.33

Model 135 (Cont'd)

CATALOG NUMBER	CURRENT RATIO	RELAY CLASS	ANSI METERING AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75°C)	CONTINUOUS THERMAL RATING FACTOR	
			B0.1	B0.2	B0.5	B0.9	B1.8		@ 30°C	@ 55°C
135-122	1,200:5*	C100	0.3	0.3	0.3	0.3	0.3	0.543	1.5	1.33
135-152	1,500:5*	C100	0.3	0.3	0.3	0.3	0.3	0.678	1.5	1.0
135-162	1,600:5*	C100	0.3	0.3	0.3	0.3	0.3	0.694	1.5	1.0
135-202	2,000:5*	C100	0.3	0.3	0.3	0.3	0.3	0.867	1.33	1.0
135-252	2,500:5*	C200	0.3	0.3	0.3	0.3	0.3	1.084	1.0	0.8
135-302	3,000:5*	C200	0.3	0.3	0.3	0.3	0.3	1.301	1.0	0.8
135-322	3,200:5*	C200	0.3	0.3	0.3	0.3	0.3	1.279	1.0	0.8
135-352	3,500:5*	C200	0.3	0.3	0.3	0.3	0.3	1.399	1.0	0.8
135-402	4,000:5*	C200	0.3	0.3	0.3	0.3	0.3	1.598	1.0	0.6
135-152	5,000:5*	C200	0.3	0.3	0.3	0.3	0.3	2.459	1.0	0.6

Approved for revenue metering by Industry Canada No. T-194 (*)



For more information, visit gevernova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.

