

MODEL 110

Current Transformer

Window Diameter 4.00"



REGULATORY AGENCY APPROVALS
UL E93779 **CS** LR89403
Manufactured to meet the requirements of ANSI/IEEE C57.13.
Classified by U.L. in accordance with IEC 44-1

Application

Relaying and metering.

Frequency

50-400 Hz

Insulation Level

600 Volt, 10 kV BIL full wave.

Terminal are brass studs No. 8-32
with one flatwasher, lockwasher and regular nut.



Order mounting bracket kit 0221B00186 separately.

Approximate weight 13 lbs.

Model 110

CATALOG NUMBER	CURRENT RATIO	V.A. ±1% CLASS	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75 °C)	CONTINUOUS THERMAL RATING FACTOR	
			B0.1	B0.2	B0.5	B0.9	B1.8		@ 30 °C	@ 55 °C
110-201	200:5	C10	0.6	1.2	1.2	2.4	-	0.085	2.0	2.0
110-301	300:5	C20	0.3	0.6	0.6	1.2	2.4	0.128	2.0	2.0
110-401	400:5	C20	0.3	0.3	0.3	0.6	1.2	0.152	2.0	2.0
110-501	500:5	C20	0.3	0.3	0.3	0.6	0.6	0.214	2.0	1.5
110-601	600:5	C50	0.3	0.3	0.3	0.3	0.6	0.256	2.0	1.5
110-801	800:5	C50	0.3	0.3	0.3	0.3	0.3	0.342	1.5	1.33
110-102	1,000:5	C100	0.3	0.3	0.3	0.3	0.3	0.427	1.5	1.0
110-122	1,200:5	C50	0.3	0.3	0.3	0.3	0.3	0.489	1.5	1.0
110-152	1,500:5	C100	0.3	0.3	0.3	0.3	0.3	0.611	1.33	1.0
110-162	1,600:5	C100	0.3	0.3	0.3	0.3	0.3	0.652	1.0	1.0
110-202	2,000:5	C100	0.3	0.3	0.3	0.3	0.3	0.815	1.0	0.8
110-252	2,500:5	C100	0.3	0.3	0.3	0.3	0.3	0.974	1.0	0.8
110-302	3,000:5	C100	0.3	0.3	0.3	0.3	0.3	1.168	1.0	0.6

Model 110



For more information, visit
gevernova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50360
 English
 250926