


MODELS 200, 201, 202, 203, 204

Current Transformers

Window Diameter

2.50", 3.50", 4.88", 5.25", 4.50"



Model 202

REGULATORY AGENCY APPROVALS



E93779



LR89403

Manufactured to meet the requirements of ANSI/IEEE C57.13.
Classified by U.L. in accordance with IEC 44-1

Application

Relaying and metering.

Features

50-400 Hz

Insulation Level

600 Volts, 10 kV BIL full wave.

Terminals are brass screws No. 10-32 with one flatwasher and lockwasher.

Multi-ratios available on request.

Excitation data available upon request.

Model 200 Window Diameter 2.50"

Approximate weight 46 lbs.

CATALOG NUMBER	CURRENT RATIO	RELAY CLASS	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75°C)	CONTINUOUS THERMAL RATING FACTOR	
			B0.1	B0.2	B0.5	B0.9	B1.8		@ 30°C	@ 55°C
200-500	50:5	C20	2.4	2.4	4.8	—	—	0.026	2.0	2.0
200-750	75:5	C20	1.2	1.2	2.4	4.8	—	0.039	2.0	2.0
200-101	100:5*	C20	0.6	1.2	1.2	2.4	4.8	0.051	2.0	2.0
200-151	150:5*	C50	0.3	0.6	0.6	1.2	2.4	0.077	2.0	2.0
200-201	200:5*	C50	0.3	0.3	0.6	0.6	1.2	0.103	2.0	2.0
200-251	250:5*	C100	0.3	0.3	0.3	0.6	1.2	0.129	2.0	2.0
200-301	300:5*	C100	0.3	0.3	0.3	0.3	0.6	0.154	2.0	2.0
200-401	400:5*	C200	0.3	0.3	0.3	0.3	0.3	0.206	2.0	1.5
200-501	500:5*	C200	0.3	0.3	0.3	0.3	0.3	0.408	1.5	1.5
200-601	600:5*	C200	0.3	0.3	0.3	0.3	0.3	0.489	1.5	1.0

*Industry Canada Approval No. T-197



GE VERNOVA



Model 201 Window Diameter 3.50"

Approximate weight 43 lbs.

CATALOG NUMBER	CURRENT RATIO	RELAY CLASS	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75°C)	CONTINUOUS THERMAL RATING FACTOR	
			B0.1	B0.2	B0.5	B0.9	B1.8		@ 30°C	@ 55°C
201-500	50:5	C10	2.4	4.8	—	—	—	0.024	2.0	2.0
201-750	75:5	C20	1.2	2.4	4.8	4.8	—	0.036	2.0	2.0
201-101	100:5*	C20	0.6	1.2	2.4	4.8	4.8	0.047	2.0	2.0
201-151	150:5*	C20	0.3	0.6	1.2	2.4	2.4	0.071	2.0	2.0
201-201	200:5*	C50	0.3	0.3	0.6	1.2	2.4	0.095	2.0	2.0
201-251	250:5*	C50	0.3	0.3	0.6	0.6	1.2	0.119	2.0	2.0
201-301	300:5*	C100	0.3	0.3	0.3	0.6	1.2	0.142	2.0	2.0
201-401	400:5*	C100	0.3	0.3	0.3	0.3	0.6	0.190	2.0	2.0
201-501	500:5*	C100	0.3	0.3	0.3	0.3	0.3	0.237	2.0	2.0
201-601	600:5*	C200	0.3	0.3	0.3	0.3	0.3	0.285	2.0	2.0
201-751	750:5*	C200	0.3	0.3	0.3	0.3	0.3	0.448	2.0	1.5
201-801	800:5*	C200	0.3	0.3	0.3	0.3	0.3	0.478	2.0	1.5

*Industry Canada Approval No. T-198

Model 202 Window Diameter 4.88"

Approximate weight 34 lbs.

CATALOG NUMBER	CURRENT RATIO	RELAY CLASS	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75°C)	CONTINUOUS THERMAL RATING FACTOR	
			B0.1	B0.2	B0.5	B0.9	B1.8		@ 30°C	@ 55°C
202-101	100:5	C20	1.2	2.4	4.8	4.8	—	0.042	2.0	2.0
202-151	150:5*	C20	0.6	1.2	2.4	2.4	4.8	0.063	2.0	2.0
202-201	200:5*	C20	0.6	0.6	1.2	1.2	2.4	0.084	2.0	2.0
202-251	250:5*	C50	0.3	0.6	0.6	1.2	2.4	0.105	2.0	2.0
202-301	300:5*	C50	0.3	0.3	0.6	0.6	1.2	0.126	2.0	2.0
202-401	400:5*	C50	0.3	0.3	0.3	0.6	0.6	0.168	2.0	2.0
202-501	500:5*	C100	0.3	0.3	0.3	0.6	0.6	0.211	2.0	2.0
202-601	600:5*	C100	0.3	0.3	0.3	0.3	0.6	0.253	2.0	2.0
202-751	750:5*	C100	0.3	0.3	0.3	0.3	0.3	0.316	2.0	1.5
202-801	800:5*	C100	0.3	0.3	0.3	0.3	0.3	0.337	2.0	1.5
202-102	1,000:5*	C200	0.3	0.3	0.3	0.3	0.3	0.421	2.0	1.5

*Industry Canada Approval No. T-199

Model 203 Window Diameter 5.25"

Approximate weight 26 lbs.

CATALOG NUMBER	CURRENT RATIO	RELAY CLASS	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75°C)	CONTINUOUS THERMAL RATING FACTOR	
			B0.1	B0.2	B0.5	B0.9	B1.8		@ 30°C	@ 55°C
203-201	200:5*	C20	0.6	0.6	1.2	2.4	—	0.064	2.0	2.0
203-251	250:5*	C20	0.3	0.6	1.2	1.2	2.4	0.081	2.0	2.0
203-301	300:5*	C50	0.3	0.3	0.6	1.2	1.2	0.097	2.0	2.0
203-401	400:5*	C50	0.3	0.3	0.3	0.6	1.2	0.129	2.0	2.0
203-501	500:5*	C50	0.3	0.3	0.3	0.3	0.6	0.161	2.0	2.0
203-601	600:5*	C100	0.3	0.3	0.3	0.3	0.6	0.193	2.0	2.0
203-751	750:5*	C100	0.3	0.3	0.3	0.3	0.3	0.242	2.0	2.0
203-801	800:5*	C100	0.3	0.3	0.3	0.3	0.3	0.324	2.0	2.0
203-102	1,000:5*	C100	0.3	0.3	0.3	0.3	0.3	0.405	2.0	1.5
203-122	1,200:5*	C200	0.3	0.3	0.3	0.3	0.3	0.486	2.0	1.5
203-152	1,500:5*	C200	0.3	0.3	0.3	0.3	0.3	0.961	1.33	1.0
203-162	1,600:5*	C200	0.3	0.3	0.3	0.3	0.3	1.292	1.33	1.0
203-202	2,000:5*	C200	0.3	0.3	0.3	0.3	0.3	1.194	1.0	0.8
203-252	2,500:5*	C200	0.3	0.3	0.3	0.3	0.3	1.493	1.0	0.8
203-302	3,000:5*	C200	0.3	0.3	0.3	0.3	0.3	1.791	1.0	0.6
203-402	4,000:5*	C100	0.3	0.3	0.3	0.3	0.3	2.214	1.0	0.6
203-502	5,000:5*	C100	0.3	0.3	0.3	0.3	0.3	3.472	0.8	0.3

*Industry Canada Approval No. T-200



Model 204 Window Diameter 4.50"

Approximate weight 35 lbs.

CATALOG NUMBER	CURRENT RATIO	RELAY CLASS	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75°C)	CONTINUOUS THERMAL RATING FACTOR	
			B0.1	B0.2	B0.5	B0.9	B1.8		@ 30°C	@ 55°C
204-101	100:5	C20	1.2	2.4	2.4	4.8	—	0.043	2.0	2.0
204-151	150:5*	C20	0.6	0.6	1.2	2.4	4.8	0.065	2.0	2.0
204-201	200:5*	C20	0.3	0.6	1.2	1.2	2.4	0.087	2.0	2.0
204-251	250:5*	C50	0.3	0.3	0.6	1.2	1.2	0.109	2.0	2.0
204-301	300:5*	C50	0.3	0.3	0.6	0.6	1.2	0.130	2.0	2.0
204-401	400:5*	C100	0.3	0.3	0.3	0.6	0.6	0.174	2.0	2.0
204-501	500:5*	C100	0.3	0.3	0.3	0.3	0.6	0.217	2.0	2.0
204-601	600:5*	C100	0.3	0.3	0.3	0.3	0.3	0.261	2.0	2.0
204-751	750:5*	C200	0.3	0.3	0.3	0.3	0.3	0.326	2.0	1.5
204-801	800:5*	C200	0.3	0.3	0.3	0.3	0.3	0.348	2.0	1.5
204-102	1,000:5*	C200	0.3	0.3	0.3	0.3	0.3	0.435	2.0	1.5

*Industry Canada Approval No. T-201

Models 200, 201, 202, 203, 204



For more information, visit
governova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50232
 English
 251015