

MODEL 137

Current Transformer

Window Diameter 5.50"



Application

Relaying and metering.

Frequency

50-400 Hz

Insulation Level

600 Volt, 10 kV BIL full wave.

Terminals are brass screws No. 10-32 with one flatwasher and lockwasher.

Order mounting bracket kit 0221B01528 separately.

Multi-ratios available on request.

Approximate weight 50 lbs.




Model 137

CATALOG NUMBER	CURRENT RATIO	RELAY CLASS	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ohms @ 75°C)	CONTINUOUS THERMAL RATING FACTOR	
			B0.1	B0.2	B0.5	B0.9	B1.8		@ 30°C	@ 55°C
137-500	50:5	C10	2.4	4.8	-	-	-	0.019	2.0	2.0
137-750	75:5	C20	1.2	2.4	4.8	-	-	0.029	2.0	2.0
137-101	100:5	C20	1.2	1.2	2.4	4.8	-	0.039	2.0	2.0
137-151	150:5*	C20	0.6	0.6	1.2	2.4	4.8	0.058	2.0	2.0
137-201	200:5*	C50	0.3	0.6	1.2	1.2	2.4	0.078	2.0	2.0
137-251	250:5*	C50	0.3	0.3	0.6	1.2	1.2	0.097	2.0	2.0
137-301	300:5*	C100	0.3	0.3	0.6	0.6	1.2	0.116	2.0	2.0
137-401	400:5*	C100	0.3	0.3	0.3	0.3	0.6	0.155	2.0	2.0
137-501	500:5*	C100	0.3	0.3	0.3	0.3	0.6	0.194	2.0	2.0
137-601	600:5*	C200	0.3	0.3	0.3	0.3	0.3	0.233	2.0	2.0
137-751	750:5*	C200	0.3	0.3	0.3	0.3	0.3	0.291	2.0	2.0
137-801	800:5*	C200	0.3	0.3	0.3	0.3	0.3	0.390	2.0	2.0
137-102	1,000:5*	C200	0.3	0.3	0.3	0.3	0.3	0.488	2.0	1.5

Model 137 (Cont'd)

CATALOG NUMBER	CURRENT RATIO	RELAY CLASS	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ohms @ 75°C)	CONTINUOUS THERMAL RATING FACTOR	
			B0.1	B0.2	B0.5	B0.9	B1.8		@ 30°C	@ 55°C
137-122	1,200:5*	C400	0.3	0.3	0.3	0.3	0.3	0.585	2.0	1.5
137-152	1,500:5*	C400	0.3	0.3	0.3	0.3	0.3	0.678	1.5	1.33
137-162	1,600:5*	C400	0.3	0.3	0.3	0.3	0.3	0.723	1.5	1.33
137-202	2,000:5*	C400	0.3	0.3	0.3	0.3	0.3	0.903	1.5	1.0
137-252	2,500:5*	C400	0.3	0.3	0.3	0.3	0.3	1.129	1.5	1.0
137-302	3,000:5*	C400	0.3	0.3	0.3	0.3	0.3	1.279	1.33	1.0
137-352	3,500:5*	C400	0.3	0.3	0.3	0.3	0.3	1.492	1.0	0.8
137-402	4,000:5*	C400	0.3	0.3	0.3	0.3	0.3	2.136	1.0	0.8
137-502	5,000:5*	C400	0.3	0.3	0.3	0.3	0.3	4.199	0.6	0.3

Approved for revenue metering by Industry Canada No. T-260



For more information, visit
gevernova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50287
 English
 251015