

MODEL 142

Current Transformer

Window Diameter 7.25"



REGULATORY AGENCY APPROVALS
UL E93779 **SP** LR89403
Manufactured to meet the requirements of ANSI/IEEE C57.13.
Classified by U.L. in accordance with IEC 44-1

Application

Relaying and metering.

Frequency

50-400 Hz.

Insulation Level

600 Volt, 10 kV BIL full wave.

Terminals are brass screws No. 10-32 with one flatwasher and lockwasher.

Order mounting bracket kit 0221B00259 separately.

Multi-ratios available on request.

Approximate weight 31 lbs.

Model 142

CATALOG NUMBER	CURRENT RATIO	RELAY CLASS	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75°C)	CONTINUOUS THERMAL RATING FACTOR	
			B0.1	B0.2	B0.5	B0.9	B1.8		@30°C	@55°C
142-500	50:5	–		–	–	–	–	0.031	2.0	2.0
142-750	75:5	–	2.4	4.8	–	–	–	0.035	2.0	2.0
142-101	100:5	C10	1.2	2.4	4.8	–	–	0.051	2.0	2.0
142-151	150:5	C10	1.2	1.2	2.4	4.8	–	0.070	2.0	2.0
142-201	200:5*	C20	0.6	0.6	1.2	2.4	4.8	0.102	2.0	2.0
142-251	250:5*	C20	0.6	0.6	1.2	1.2	2.4	0.127	2.0	2.0
142-301	300:5*	C30	0.3	0.3	0.6	1.2	2.4	0.153	2.0	2.0
142-401	400:5*	C50	0.3	0.3	0.3	0.6	1.2	0.196	2.0	2.0
142-501	500:5*	C50	0.3	0.3	0.3	0.6	0.6	0.252	2.0	2.0
142-601	600:5*	C50	0.3	0.3	0.3	0.3	0.6	0.255	2.0	2.0
142-751	750:5*	C100	0.3	0.3	0.3	0.3	0.3	0.304	2.0	1.5
142-801	800:5*	C100	0.3	0.3	0.3	0.3	0.3	0.336	2.0	1.5
142-102	1,000:5*	C100	0.3	0.3	0.3	0.3	0.3	0.486	2.0	1.5
142-122	1,200:5*	C100	0.3	0.3	0.3	0.3	0.3	0.735	1.5	1.0





Model 142 (Cont'd)

CATALOG NUMBER	CURRENT RATIO	RELAY CLASS	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75°C)	CONTINUOUS THERMAL RATING FACTOR	
			B0.1	B0.2	B0.5	B0.9	B1.8		@30°C	@55°C
142-152	1,500:5*	C200	0.3	0.3	0.3	0.3	0.3	0.918	1.5	1.0
142-162	1,600:5*	C200	0.3	0.3	0.3	0.3	0.3	0.979	1.33	1.0
142-202	2,000:5*	C200	0.3	0.3	0.3	0.3	0.3	0.544	2.0	1.5
142-252	2,500:5*	C200	0.3	0.3	0.3	0.3	0.3	1.066	1.5	1.0
142-302	3,000:5*	C200	0.3	0.3	0.3	0.3	0.3	1.280	1.0	0.8
142-322	3,200:5*	C200	0.3	0.3	0.3	0.3	0.3	1.365	1.0	0.8
142-352	3,500:5*	C200	0.3	0.3	0.3	0.3	0.3	1.493	1.0	0.8
142-402	4,000:5*	C200	0.3	0.3	0.3	0.3	0.3	0.986	1.33	1.0
142-502	5,000:5*	C200	0.3	0.3	0.3	0.3	0.3	1.023	1.33	1.0
142-602	6,000:5*	C200	0.3	0.3	0.3	0.3	0.3	2.298	1.0	0.6

Approved for revenue metering by Industry Canada No. AE-0650

Model 142



For more information, visit
gevernova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50639
 English
 251014