

MODEL 2DARL

Current Transformer

Window Diameter 1.00"



Application

Ammeters, wattmeters and cross current compensation.

Rating Factor

1.0 @ 30°C. amb.

Frequency

50-400 Hz.

Insulation Level

600 Volts, 10 kV BIL full wave



Flexible leads are UL 1015, 105°C, CSA approved, #16 AWG, 24" long. Non-standard, lead length can be specified.

Approximate weight 0.9 lbs.

Data Table

CATALOG NUMBER	CURRENT RATIO	V.A. ±1% CLASS	ANSI METERING CLASS AT 60 Hz			SECONDARY WINDING RESISTANCE (Ω @75°C)
			B0.1	B0.2	B0.5	
2DARL-500	50:5	2% 2.5	4.8	—	—	0.008
2DARL-600	60:5	2.5	2.4	—	—	0.011
2DARL-750	75.5	3.5	1.2	2.4	—	0.015
2DARL-800	80.5	4.0	1.2	2.4	—	0.016
2DARL-101	100.5	5.0	1.2	2.4	—	0.018
2DARL-121	120.5	5.0	1.2	2.4	—	0.022
2DARL-1250	125.5	5.0	0.6	1.2	—	0.028
2DARL-151	150.5	10.0	0.6	0.6	—	0.031
2DARL-201	200.5	12.5	0.3	0.6	1.2	0.047
2DARL-251	250.5	15.0	0.3	0.3	0.6	0.074
2DARL-301	300.5	20.0	0.3	0.3	0.6	0.089

Model 2DARL



For more information, visit gevernova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GEA-N50346
English
250917