

MODEL 306MR

Current Transformer with Multi-Ratio

Window Diameter 4.50"

Application

Relaying.

Frequency



50-400 Hz.

Insulation Level

600 Volt, 10 kV BIL full wave.

Model 306MR

CATALOG NUMBER	RELAY CLASS	CONTINUOUS THERMAL RATING FACTOR	
		@ 30°C	@ 55°C
306-601MR	C100	2.0	1.0
306-122MR	C200	1.5	1.0
306-202MR	C400	1.5	1.0
306-302MR	C400	1.33	1.0



REGULATORY AGENCY APPROVALS

UL E93779 **CSA** LR89403

Manufactured to meet the requirements of ANSI/IEEE C57.13.
Classified by U.L. in accordance with IEC 44-1


Terminals are brass screws No. 10-32 with one flatwasher and lockwasher.

The transformer winding is arranged so that the turns are fully distributed between all taps.


Order mounting bracket kit 0221B01527 separately.

Approximate weight 27 lbs.


Model 306MR




Model 306-122MR



Model 306-202MR



Model 306-302MR



For more information, visit
[governova.com/grid-solutions](https://www.governova.com/grid-solutions)

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50770
English
251008