


MODEL 3P10

Current Transformer

Window Size 1.58" x 0.26"



REGULATORY AGENCY APPROVALS
 E93779
Manufactured to meet the requirements of ANSI/IEEE C57.13.
Classified by U.L. in accordance with IEC 44-1

Application

3 phase relaying and motor overload protection

Frequency

50-400 Hz.

Insulation Level

600 Volts, 10 kV BIL full wave.

Continuous Thermal Current Rating Factor:

1.0 at 30°C ambient.
0.75 at 55°C ambient.

Secondary leads are UL 1015, 105°C.,
CSA approved, No. 16 AWG, 24" long.


Approximate weight 4 lbs.

Data Table Model 3P10

CATALOG NUMBER	CURRENT RATIO	VA FOR ± 1% CLASS	SECONDARY WINDING RESISTANCE (Ω @ 75 °C)
3P10-201	200:5	7.5	0.056
3P10-251	250:5	10.0	0.071
3P10-301	300:5	12.5	0.089
3P10-401	400:5	15.0	0.113
3P10-501	500:5	20.0	0.186
3P10-601	600:5	25.0	0.223

Note: Captive slots on tap of transformer case can be used for attaching auxiliary device mounting plate, (not supplied).
Originally designed for use with molded case circuit breakers and motor starters with 3.12" bus center lines.
Can be mounted directly on bus bar and held in place with roll pins inserted in bus.

Model 3P10



For more information, visit
gevernova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50616
 English
 250911