


MODEL 3P4

Current Transformer

Window Diameter 1.56"



REGULATORY AGENCY APPROVALS
 E93779  LR89403
 Manufactured to meet the requirements of ANSI/IEEE C57.13.
 Classified by U.L. in accordance with IEC 44-1

Application

3 phase metering and other switchboard applications.

Frequency

50-400 Hz.

Insulation Level

600 Volt, 10 kV BIL full wave.

Terminals are brass studs No. 8-32 with one flatwasher, lockwasher and regular nut.

Transformers can be ordered with secondary leads configured in various ways (consult factory).

Approximate weight 6.75 lbs.

Data Table: Model 3P4



CATALOG NUMBER	CURRENT RATIO	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75°C)
		B0.1	B0.2	B0.5	B0.9	B1.8	
3P4-500	50:5	4.8	-	-	-	-	0.011
3P4-101	100:5	1.2	2.4	-	-	-	0.023
3P4-151	150:5	0.6	1.2	2.4	-	-	0.034
3P4-201	200:5	0.6	0.6	1.2	2.4	-	0.045
3P4-251	250:5	0.6	0.6	1.2	2.4	2.4	0.057
3P4-301	300:5	0.3	0.3	0.6	1.2	2.4	0.068
3P4-401	400:5	0.3	0.3	0.6	1.2	1.2	0.091
3P4-501	500:5	0.3	0.3	0.6	0.6	1.2	0.113
3P4-601	600:5	0.3	0.3	0.6	0.6	1.2	0.136
3P4-751	750:5	0.3	0.3	0.6	0.6	0.6	0.170
3P4-801	800:5	0.3	0.3	0.6	0.6	0.6	0.181
3P4-102	1,000:5	0.3	0.3	0.3	0.6	0.6	0.226



GE VERNOVA



Model 3P30



For more information, visit
gevernova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.

GEA-N50456
English
251016



GE VERNOVA