

MODEL 3P22

Current Transformer

Window Diameter 0.44"



For Horizontal Mounting

Application

Instrumentation & Metering. Idea for 3-phase motor loads.

Frequency

60 Hz.

Feature

CT can be mounted directly to cable with nylon thumb screws

Insulation Level

10 kV BIL, 600 Vac


Leads are No. 16 AWG, 24" long
Approximate weight 0.6 lbs

Data Table Model 3P22

CATALOG NUMBER	CURRENT RATIO	ACCURACY (60 Hz.)	RATING FACTOR
3P22-500-1.0	50:1.0	2%, 0.1VA	1.0
3P22-101-1.0	100:1.0	2%, 0.1VA	1.0

* Consult factory for additional ratios.

Model 3P22



For more information, visit
gevernova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50575
 English
 251015