


MODEL 3P40

Current Transformer

Window Diameter 1.75"



Application

3 phase relay, metering and motor overload protection.

Frequency

50-400 Hz.

Insulation Level

600 Volts, 10 kV BIL full wave.



Terminals are brass studs No. 8-32 with one flatwasher, lockwasher and regular nut.

Approximate weight 14 lbs.

Data Table: Model 3P40

CATALOG NUMBER	CURRENT RATIO	RELAY CLASS	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75°C)
			B0.1	B0.2	B0.5	B0.9	B1.8	
3P40—101	100:5	—	0.6	1.2	2.4	—	—	0.033
3P40—151	150:5	—	0.6	0.6	1.2	2.4	—	0.049
3P40—201	200:5	C10	0.3	0.6	0.6	1.2	2.4	0.082
3P40—251	250:5	C10	0.3	0.3	0.6	0.6	1.2	0.103
3P40—301	300:5	C20	0.3	0.3	0.3	0.6	1.2	0.124
3P40—401	400:5	C20	0.3	0.3	0.3	0.6	1.2	0.131
3P40—501	500:5	C20	0.3	0.3	0.3	0.3	0.6	0.163

Model 3P40



For more information, visit
gevernova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.

GEA-N50537
English
251008



GE VERNOVA