

MODEL 3P665

Current Transformer

Window Size 2.63" x 4.88"



Application

3 phase metering.

Frequency

50-400 Hz.

Insulation Level

600 Volts, 10 kV BIL full wave.

The core and coil assembly is encased in a thermoplastic shell.



Four 12 gauge wires exit right sid (H1 side). Wire length is 24" long, labeled as shown.

Approximate weight 7.5 lbs

Data Table: Model 3P665

CATALOG NUMBER	CURRENT RATIO	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75 °C)
		B0.1	B0.2	B0.5	B0.9	B1.8	
3P665-162	1600:5	0.3	0.3	0.6	0.6	1.2	0.231
3P665-202	2000:5	0.3	0.3	0.3	0.6	0.6	0.289
3P665-242	2400:5	0.3	0.3	0.3	0.3	0.6	0.431
3P665-252	2500:5	0.3	0.3	0.3	0.3	0.3	0.449
3P665-302	3000:5	0.3	0.3	0.3	0.3	0.3	0.539
3P665-322	3200:5	0.3	0.3	0.3	0.3	0.3	0.574
3P665-352	3500:5	0.3	0.3	0.3	0.3	0.3	0.712
3P665-402	4000:5	0.3	0.3	0.3	0.3	0.3	0.813

Model 3P665



For more information, visit
gevernova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GEA-N50636
English
250911