

MODEL 3P667

Current Transformer

Window Diameter 2.75"



Application

3 phase metering and motor overload protection.

Frequency

50-400 Hz.

Insulation level

600 Volts, 10 kV BIL full wave.

Terminals are brass studs No. 8-32 with one flatwasher and regular nut.



Flexible leads UL 1015, 105 °C, CSA approved, No. 16 AWG, 24" long are available.

Approximate weight 15 lbs.

Data Table: Model 3P667

CATALOG NUMBER	CURRENT RATIO	ANSI METERING CLASS AT 60 HZ					SECONDARY WINDING RESISTANCE (Ω @ 75°C)
		B0.1	B0.2	B0.5	B0.9	B1.8	
3P667—500	50:5	4.8	—	—	—	—	0.013
3P667—750	75:5	2.4	4.8	—	—	—	0.019
3P667—101	100:5	1.2	2.4	—	—	—	0.028
3P667—151	150:5	0.6	1.2	2.4	—	—	0.041
3P667—201	200:5	0.3	0.6	1.2	—	—	0.055
3P667—301	300:5	0.3	0.3	0.6	1.2	—	0.083
3P667—401	400:5	0.3	0.3	0.3	0.6	1.2	0.111
3P667—501	500:5	0.3	0.3	0.3	0.6	1.2	0.138
3P667—601	600:5	0.3	0.3	0.3	0.3	0.6	0.166

Model 3P667



For more information, visit
gevernova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50538
 English
 250916