

MODEL 521

Current Transformer

Window Size 1.56" x 0.59"

Application

Metering.

Frequency

50-400 Hz.

Insulation Level

600 Volts, 10 kV BIL full wave.

Model 521

CATALOG NUMBER	CURRENT RATIO	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75 °C)
		B0.1	B0.2	B0.5	B0.9	B1.8	
521-101	100:5	1.2	2.4	–	–	–	0.018
521-151	150:5	0.6	1.2	2.4	–	–	0.033
521-201	200:5	0.3	0.6	2.4	2.4	–	0.047
521-251	250:5	0.3	0.6	1.2	2.4	–	0.059
521-301	300:5	0.3	0.3	0.6	1.2	–	0.069
521-401	400:5	0.3	0.3	0.3	0.6	1.2	0.088
521-501	500:5	0.3	0.3	0.3	0.6	1.2	0.115
521-601	600:5	0.3	0.3	0.3	0.6	1.2	0.165
521-751	750:5	0.3	0.3	0.3	0.3	0.6	0.206





Continuous Thermal Rating Factor

1.33 at 30 °C. amb.,
1.0 at 55 °C. amb.

Terminals are brass studs No. 10-32 with one flatwasher, lockwasher and regular nut.

Approximate weight 3.5 lbs.

Model 521



For more information, visit
[gevernova.com/grid-solutions](https://www.gevernova.com/grid-solutions)

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GEA-N50655
English
250917