

MODEL 531

Current Transformer

Window Size 4.06" x 3.06"

Application

Metering.

Frequency

50-400 Hz.

Insulation Level

600 Volts, 10 kV BIL full wave.

Model 531

CATALOG NUMBER	CURRENT RATIO	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75°C)
		B0.1	B0.2	B0.5	B0.9	B1.8	
531-101	100:5	4.8	4.8	-	-	-	0.026
531-151	150:5	2.4	2.4	4.8	-	-	0.039
531-201	200:5	1.2	2.4	4.8	4.8	-	0.052
531-251	250:5	1.2	1.2	2.4	4.8	4.8	0.065
531-301	300:5	0.6	1.2	2.4	2.4	4.8	0.079
531-401	400:5	0.6	0.6	1.2	2.4	2.4	0.105
531-501	500:5	0.3	0.6	0.6	1.2	2.4	0.131
531-601	600:5	0.3	0.3	0.6	1.2	1.2	0.157
531-751	750:5	0.3	0.3	0.6	0.6	1.2	0.196
531-801	800:5	0.3	0.3	0.6	0.6	1.2	0.209
531-102	1,000:5	0.3	0.3	0.3	0.6	0.6	0.262
531-122	1,200:5	0.3	0.3	0.3	0.3	0.6	0.314



Continuous Thermal Current Rating Factor



1.33 at 30°C. amb., 1.0 at 55°C. amb.

Terminals are brass screws No. 8-32 with one flatwasher and lockwasher.

Cast resin construction.

Approximate weight 3 lbs.

Model 531



For more information, visit
[gevernova.com/grid-solutions](https://www.gevernova.com/grid-solutions)

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50738
 English
 250918