



Model 543 - Window Size 0.53" X 1.53"

CATALOG NUMBER	CURRENT RATIO	RELAY CLASS	ANSI METERING CLASS AT 60 Hz		SECONDARY WINDING RESISTANCE (Ω @ 75 °C)
			B0.1	B0.2	
543-101	100:5	C10	1.2	2.4	0.045
543-151	150:5	C20	0.6	1.2	0.053
543-201	200:5	C20	0.6	0.6	0.089
543-251	250:5	C20	0.3	0.6	0.112
543-301	300:5	C20	0.3	0.3	0.134
543-401	400:5	C50	0.3	0.3	0.142
543-501	500:5	C50	0.3	0.3	0.281
543-601	600:5	C50	0.3	0.3	0.337
543-801	800:5	C50	0.3	0.3	0.564




Model 544 - Window Size 0.53" X 1.53"

CATALOG NUMBER	CURRENT RATIO	RELAY CLASS	ANSI METERING CLASS AT 60 Hz		SECONDARY WINDING RESISTANCE (Ω @ 75 °C)
			B0.1	B0.2	
544-601	600:5	C100	0.3	0.3	0.398
544-801	800:5	C100	0.3	0.3	0.666




Model 545 - Window Size 0.53" X 3.0"

CATALOG NUMBER	CURRENT RATIO	RELAY CLASS	ANSI METERING CLASS AT 60 Hz		SECONDARY WINDING RESISTANCE (Ω @ 75 °C)
			B0.1	B0.2	
544-201	200:5	C10	0.6	1.2	0.089
544-251	250:5	C10	0.6	1.2	0.112
544-301	300:5	C20	0.6	0.6	0.134
544-401	400:5	C20	0.3	0.6	0.179
544-501	500:5	C20	0.3	0.3	0.281
544-601	600:5	C20	0.3	0.3	0.337
544-801	800:5	C50	0.3	0.3	0.450
545-102	1000:5	C50	0.3	0.3	0.522
545-122	1200:5	C50	0.3	0.3	0.627
545-152	1500:5	C50	0.3	0.3	0.601
545-162	1600:5	C50	0.3	0.3	0.641




Model 546 - Window Size 0.53" X 3.03"

CATALOG NUMBER	CURRENT RATIO	RELAY CLASS	ANSI METERING CLASS AT 60 HZ		SECONDARY WINDING RESISTANCE (Ω @ 75 °C)
			B0.1	B0.2	
546-102	1,000:5	C100	0.3	0.3	0.446
546-122	1,200:5	C100	0.3	0.3	0.675
546-152	1,500:5	C100	0.3	0.3	0.480
546-162	1,600:5	C100	0.3	0.3	0.512




Model 547 - Window Size 0.53" X 4.03"

CATALOG NUMBER	CURRENT RATIO	RELAY CLASS	ANSI METERING CLASS AT 60 HZ		SECONDARY WINDING RESISTANCE (Ω @ 75 °C)
			B0.1	B0.2	
547-251	250:5	C10	0.6	1.2	0.112
547-301	300:5	C20	0.6	0.6	0.134
547-401	400:5	C20	0.3	0.6	0.179
547-501	500:5	C20	0.3	0.3	0.281
547-601	600:5	C20	0.3	0.3	0.337
547-801	800:5	C50	0.3	0.3	0.450
547-102	1,000:5	C50	0.3	0.3	0.522
547-122	1,200:5	C50	0.3	0.3	0.627
547-152	1,500:5	C50	0.3	0.3	0.601
547-162	1,600:5	C50	0.3	0.3	0.641
547-202	2,000:5	C50	0.3	0.3	0.513



Model 548 - Window Size 0.53" X 4.03"

CATALOG NUMBER	CURRENT RATIO	RELAY CLASS	ANSI METERING CLASS AT 60 HZ		SECONDARY WINDING RESISTANCE (Ω @ 75 °C)
			B0.1	B0.2	
548-102	1,000:5	C100	0.3	0.3	0.446
548-122	1,200:5	C100	0.3	0.3	0.675
548-152	1,500:5	C100	0.3	0.3	0.480
548-162	1,600:5	C100	0.3	0.3	0.512
548-202	2,000:5	C100	0.3	0.3	0.640



For more information, visit
gevernova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50479
English
250911