

MODEL 562

Current Transformer

Window Size 4.00" x 5.38"



Application

Metering.

Frequency

50-400 Hz.

Insulation Level

600 Volts, 10 kV BIL full wave.

Insulation System

Temperature Class H (180°C.)

Continuous Thermal Current Rating Factor

1.33 at 30°C. amb.,
1.0 at 55°C. amb.

Terminals are brass screws No. 10-32 with one flatwasher and lockwasher.



Approximate weight 8 lbs

Model 562

CATALOG NUMBER	CURRENT RATIO	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75°C)
		B0.1	B0.2	B0.5	B0.9	B1.8	
562-202	2,000:5	0.3	0.3	0.3	0.6	0.6	0.345
562-252	2,500:5	0.3	0.3	0.3	0.3	0.6	0.431
562-302	3,000:5	0.3	0.3	0.3	0.3	0.6	0.517
562-322	3,200:5	0.3	0.3	0.3	0.3	0.6	0.552
562-352	3,500:5	0.3	0.3	0.3	0.3	0.3	0.604
562-402	4,000:5	0.3	0.3	0.3	0.3	0.3	0.600

Approved for revenue metering by Industry Canada No. AE-0659 (*)

Model 562



For more information, visit
governova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50374
 English
 251015