

MODEL 563

Current Transformer

Window Size 4.00" x 5.38"

Application

Relaying and metering.

Frequency

50-400 Hz.

Insulation Level

600 Volts, 10 kV BIL full wave.

Model 563

CATALOG NUMBER	CURRENT RATIO	RELAY CLASS	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75 °C)
			B0.1	B0.2	B0.5	B0.9	B1.8	
563-202	2,000:5	C50	0.3	0.3	0.3	0.3	0.3	0.995
563-252	2,500:5	C50	0.3	0.3	0.3	0.3	0.3	1.244
563-302	3,000:5	C20	0.3	0.3	0.3	0.3	0.3	1.382
563-322	3,200:5	C20	0.3	0.3	0.3	0.3	0.3	1.474
563-402	4,000:5	C20	0.3	0.3	0.3	0.3	0.3	1.842



Insulation System

Temperature Class H (180°C.)

Continuous Thermal Current Rating Factor



1.33 at 30 °C. amb.,
1.0 at 55 °C. amb.

Terminals are brass screws No. 10-32 with one flatwasher and lockwasher.

Approximate weight 12 lbs.



Model 563



For more information, visit
[gevernova.com/grid-solutions](https://www.gevernova.com/grid-solutions)

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50577
 English
 251015