

MODEL 575

Current Transformer

Window Size 0.75" x 3.25"

Application

Metering.

Frequency

50-400 Hz.

Insulation Level

600 Volts, 10 kV BIL full wave.

Model 575

CATALOG NUMBER	CURRENT RATIO	ANSI METERING CLASS AT 60 Hz		SECONDARY WINDING RESISTANCE (Ohms @ 75°C)
		B0.1	B0.2	
575-101	100:5	2.4	4.8	0.010
575-151	150:5	1.2	2.4	0.018
575-201	200:5	1.2	1.2	0.033
575-251	250:5	0.6	1.2	0.045
575-301	300:5	0.6	0.6	0.056
575-401	400:5	0.6	0.6	0.078
575-501	500:5	0.6	0.6	0.098
575-601	600:5	0.6	0.6	0.117
575-801	800:5	0.3	0.3	0.157
575-102	1,000:5	0.3	0.3	0.152



Continuous Thermal Current Rating Factor


1.33 at 30°C. amb.,
1.0 at 55°C. amb.

Terminals are brass studs No. 10-32 with one flatwasher, lockwasher and regular nut.

Approximate weight 2.5 lbs.

Excitation data available upon request.

Model 575



For more information, visit
gevernova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50514
English
250930