

MODELS

569TL, 569TS

Current Transformers

Window Size 9.50" x 3.75"



TL Style



TS Style

REGULATORY AGENCY APPROVALS



E93779



LR89403

Manufactured to meet the requirements of ANSI/IEEE C57.13.
Classified by U.L. in accordance with IEC 44-1

Application

Metering.

Frequency

50-400 Hz.

Insulation Level

600 Volts, 10 kV BIL full wave.

Continuous Thermal Current Rating Factor

1.33 at 30°C. amb., 1.0 at 55°C. amb.

TL-Terminals are brass studs No. 10-32 with one flatwasher, lockwasher and regular nut.

TS-Terminals are brass screws No. 10-32 with one flatwasher, lockwasher and regular nut.

Approximate weight 5 lbs.

Models 569TL, 569TS

CATALOG NUMBER	CURRENT RATIO	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75°C)
		B0.1	B0.2	B0.5	B0.9	B1.8	
569**202	2,000:5	0.3	0.3	0.3	0.6	0.6	0.417
569**252	2,500:5	0.3	0.3	0.3	0.3	0.6	0.521
569**302	3,000:5	0.3	0.3	0.3	0.3	0.6	0.625
569**322	3,200:5	0.3	0.3	0.3	0.3	0.6	0.667
569**352	3,500:5	0.3	0.3	0.3	0.3	0.6	0.730
569**402	4,000:5	0.3	0.3	0.3	0.3	0.6	0.834
569**502	5,000:5	0.3	0.3	0.3	0.3	0.6	1.042


**Note: When ordering, prefix Cat No. with model designation required i.e. 569TL-201, or 569TS-201, etc.




GE VERNOVA




Model 569TL , 569TS



TL Style



TS Style



For more information, visit
governova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50434
English
251016