

MODEL 570

Current Transformer

Window Size 3.56" x 0.79"

Application

Metering.

Frequency

50-400 Hz.

Insulation Level

600 Volts, 10 kV BIL full wave.

Model 570

CATALOG NUMBER	CURRENT RATIO	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75 °C)
		B0.1	B0.2	B0.5	B0.9	B1.8	
570-201	200:5	1.2	2.4	–	–	–	0.042
570-251	250:5	1.2	1.2	2.4	–	–	0.053
570-301	300:5	0.6	1.2	1.2	2.4	–	0.063
570-401	400:5	0.6	0.6	1.2	2.4	2.4	0.084
570-501	500:5	0.3	0.6	1.2	1.2	2.4	0.106
570-601	600:5	0.3	0.3	0.6	1.2	1.2	0.127
570-751	750:5	0.3	0.3	0.6	0.6	1.2	0.158
570-801	800:5	0.3	0.3	0.6	0.6	1.2	0.169
570-102	1,000:5	0.3	0.3	0.3	0.6	0.6	0.211



REGULATORY AGENCY APPROVALS
UL E93779 **SP** LR89403
Manufactured to meet the requirements of ANSI/IEEE C57.13.
Classified by U.L. in accordance with IEC 44-1



Continuous Thermal Current Rating Factor

1.33 at 30 °C. amb.,
1.0 at 55 °C. amb.

Terminals are brass studs No. 10-32 with one flatwasher, lockwasher and regular nut.

Approximate weight 3 lbs.

Model 570



For more information, visit
[gevernova.com/grid-solutions](https://www.gevernova.com/grid-solutions)

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50615
English
250911