

MODEL 576

Current Transformer

Window Size 2.00" x 5.25"



Application

Metering.

Frequency

50-400 Hz.

Insulation Level

600 Volts, 10 kV BIL full wave.

Continuous Thermal Current Rating Factor

1.33 at 30 °C. amb.,
1.0 at 55 °C. amb.

Terminals are brass studs No. 10-32 with one flatwasher, lockwasher and regular nut.

Approximate weight 3.5 lbs.



Model 576

CATALOG NUMBER	CURRENT RATIO	ANSI METERING CLASS AT 60 Hz			SECONDARY WINDING RESISTANCE (Ω @ 75 °C)
		BO.1	BO.2	BO.5	
576-102	1,000:5	0.3	0.3	0.6	0.179
576-122	1,200:5	0.3	0.3	0.6	0.215
576-152	1,500:5	0.3	0.3	0.6	0.173
576-162	1,600:5	0.3	0.3	0.6	0.217
576-202	2,000:5	0.3	0.3	0.3	0.272
576-252	2,500:5	0.3	0.3	0.3	0.339
576-302	3,000:5	0.3	0.3	0.3	0.468
*576-402	4,000:5	0.3	0.3	0.3	0.945
**576-502	5,000:5	0.3	0.3	0.3	1.462
**576-602	6,000:5	0.3	0.3	0.3	2.168

* Rating Factor 0.62 at 30°C.

** Rating Factor 0.55 at 30°C.

Model 576



For more information, visit
[gevernova.com/grid-solutions](https://www.gevernova.com/grid-solutions)

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50428
 English
 250916