

MODEL 571

Current Transformer

Window Size 3.58" x 4.13"



Application

Metering.

Frequency

50-400 Hz.

Insulation Level

600 Volts, 10 kV BIL full wave.

Continuous Thermal Current Rating Factor

1.33 at 30 °C. amb., 1.0 at 55 °C. amb.



Terminals are brass studs No. 10-32 with one flatwasher, lockwasher and regular nut.

Approximate weight 4 lbs.

Model 571

CATALOG NUMBER	CURRENT RATIO	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75°C)
		B0.1	B0.2	B0.5	B0.9	B1.8	
571-801	800:5	0.6	0.6	0.6	1.2	2.4	0.143
571-102	1,000:5	0.3	0.3	0.6	0.6	1.2	0.179
571-122	1,200:5	0.3	0.3	0.6	0.6	1.2	0.215
571-152	1,500:5	0.3	0.3	0.3	0.6	0.6	0.337
571-162	1,600:5	0.3	0.3	0.3	0.6	0.6	0.360
571-202	2,000:5	0.3	0.3	0.3	0.3	0.6	0.497
571-252	2,500:5	0.3	0.3	0.3	0.3	0.3	0.622
571-302	3,000:5	0.3	0.3	0.3	0.3	0.3	0.746
571-322	3,200:5	0.3	0.3	0.3	0.3	0.3	0.872

Model 571



For more information, visit
gevernova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50467
 English
 251013