

MODEL 5DRL

Current Transformer

Window Diameter 1.56"



Application

Ammeters, wattmeters and cross current compensation.

Frequency

50-400 Hz.

Insulation Level

600 Volt, 10 kV BIL full wave.

Flexible leads are UL 1015, 105 °C, CSA approved, #16 AWG, 24" long.

Non-standard, lead length can be specified.



Approximate weight 2 lbs.

Model 5DRL

CATALOG NUMBER	CURRENT RATIO	ACCURACY AT 60 Hz	BURDEN VA AT 60 Hz
5DRL-500	50:5	±2%	2.5
5DRL-600	60:5	±1%	2.5
5DRL-750	75:5	±1%	3.5
5DRL-101	100:5	±1%	5.0
5DRL-151	150:5	±1%	10.0
5DRL-201	200:5	±1%	12.5
5DRL-251	250:5	±1%	20.0
5DRL-301	300:5	±1%	25.0

CATALOG NUMBER	CURRENT RATIO	ACCURACY AT 60 Hz	BURDEN VA AT 60 Hz
5DRL-401	400:5	±1%	40
5DRL-501	500:5	±1%	50
5DRL-601	600:5	±1%	60
5DRL-751	750:5	±1%	60
5DRL-801	800:5	±1%	60
5DRL-102	1000:5	±1%	75
5DRL-122	1200:5	±1%	90

Model 5DRL



For more information, visit
gevernova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50630
English
250911