

MODEL 624

Current Transformer

Window Diameter 5.25"

Application

Relaying and metering.

Frequency

50-400 Hz.

Insulation Level

600 Volts, 10 kV BIL full wave.



REGULATORY AGENCY APPROVALS



Manufactured to meet the requirements of ANSI/IEEE C57.13.
Classified by U.L. in accordance with IEC 44-1

Continuous Thermal Current Rating Factor

50:5-3200:5: 1.33 at 30°C. amb., 1.0 at 55°C. amb.

4000:5: 1.0 at 30°C. amb., 0.8 at 55°C. amb.

5000:5: 0.8 at 30°C. amb., 0.6 at 55°C. amb.

Secondary terminals are brass screws No. 10-32 with one flatwasher, lockwasher, accessible from either side.



Multi-ratios available on request. Consult Factory

Approximate weight 68 lbs.

Model 624

CATALOG NUMBER	CURRENT RATIO	RELAY CLASS	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75°C)
			B0.1	B0.2	B0.5	B0.9	B1.8	
624-500	50:5	C20	2.4	4.8	-	-	-	0.031
624-750	75:5	C20	1.2	2.4	4.8	4.8	-	0.047
624-101	100:5	C50	0.6	1.2	2.4	4.8	4.8	0.062
624-151	150:5	C50	0.6	0.6	1.2	2.4	4.8	0.096
624-201	200:5	C100	0.3	0.6	1.2	1.2	2.4	0.127
624-251	250:5	C100	0.3	0.6	0.6	1.2	2.4	0.159
624-301	300:5	C100	0.3	0.3	0.6	0.6	1.2	0.191
624-401	400:5	C200	0.3	0.3	0.3	0.3	0.6	0.255
624-501	500:5	C200	0.3	0.3	0.3	0.3	0.6	0.319
624-601	600:5	C200	0.3	0.3	0.3	0.3	0.3	0.382
624-751	750:5	C200	0.3	0.3	0.3	0.3	0.3	0.478
624-801	800:5	C200	0.3	0.3	0.3	0.3	0.3	0.510
624-102	1000:5	C400	0.3	0.3	0.3	0.3	0.3	0.637
624-122	1200:5	C400	0.3	0.3	0.3	0.3	0.3	0.765
624-152	1500:5	C400	0.3	0.3	0.3	0.3	0.3	0.918
624-162	1600:5	C400	0.3	0.3	0.3	0.3	0.3	0.979
624-202	2000:5	C400	0.3	0.3	0.3	0.3	0.3	1.224
624-252	2500:5	C800	0.3	0.3	0.3	0.3	0.3	1.529
624-302	3000:5	C800	0.3	0.3	0.3	0.3	0.3	1.702
624-322	3200:5	C800	0.3	0.3	0.3	0.3	0.3	1.912
624-402	4000:5	C800	0.3	0.3	0.3	0.3	0.3	2.185
624-502	5000:5	C800	0.3	0.3	0.3	0.3	0.3	3.428

Model 624



For more information, visit
gevernova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50710
 English
 250916