

MODEL 790MR

Current Transformer with Multi-Ratio

Window Diameter 5.00"



REGULATORY AGENCY APPROVALS



Manufactured to meet the requirements of ANSI/IEEE C57.13.
Classified by U.L. in accordance with IEC 44-1

Application

Relaying.

Frequency

50-400 Hz.

Insulation Level

0.6 kV, 10 kV BIL full wave.


Model 790MR

CATALOG NUMBER	RELAY CLASS	CONTINUOUS THERMAL CURRENT RATING FACTOR @ 30° C
790-122MR	C100	1.5
790-202MR	C100	1.5

Continuous Thermal Current Rating Factor

Secondary terminals are brass screws No. 10-32 with one flatwasher, lockwasher.


Approximate weight 15 lbs.




CONNECTION DIAGRAM

Model 790MR

Model 790-202MR



BASEPLATE HAS
(4) 0.47 SQUARE HOLES
FOR CAPTIVE NUTS



For more information, visit
[gevernova.com/grid-solutions](https://www.gevernova.com/grid-solutions)

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50638
English
250911