

MODEL 785

Current Transformer

Window Diameter 6.50"

Application

Relaying and metering.

Frequency

50-400 Hz.

Insulation Level

0.6 kV, BIL 10 kV full wave.



REGULATORY AGENCY APPROVALS



E93779



LR89403

Manufactured to meet the requirements of ANSI/IEEE C57.13.
Classified by U.L. in accordance with IEC 44-1

Continuous Thermal Current Rating Factor

50:5-1,200:5 & 2,000:5

2.0 at 30 °C. amb., 1.5 at 55 °C.

1,500:5,1,600:5 & ,2500:5

1.5 at 30 °C. amb., 1.33 at 55 °C. amb.

3,000:5-4,000:5

1.33 at 30 °C. amb., 1.0 at 55 °C. amb.

Secondary terminals are brass screws No. 10-32 with one flatwasher, lockwasher, accessible from either side. Approximate weight 58 lbs.

Excitation data available upon request.



GE VERNOVA




Model 785

CATALOG NUMBER	CURRENT RATIO	RELAY CLASS	ANSI METERING CLASS AT 60 Hz				
			B0.1	B0.2	B0.5	B0.9	B1.8
785-500	50:5	C10	2.4	4.8	-	-	-
785-750	75:5	C20	1.2	1.2	4.8	-	-
785-101	100:5*	C20	0.6	1.2	2.4	-	-
785-151	150:5*	C50	0.6	0.6	1.2	2.4	-
785-201	200:5*	C50	0.3	0.3	0.6	1.2	2.4
785-251	250:5*	C50	0.3	0.3	0.6	1.2	2.4
785-301	300:5*	C100	0.3	0.3	0.3	0.6	1.2
785-401	400:5*	C100	0.3	0.3	0.3	0.6	1.2
785-501	500:5*	C100	0.3	0.3	0.3	0.3	0.6
785-601	600:5*	C200	0.3	0.3	0.3	0.3	0.6
785-751	750:5*	C200	0.3	0.3	0.3	0.3	0.3
785-801	800:5*	C200	0.3	0.3	0.3	0.3	0.3
785-102	1,000:5*	C200	0.3	0.3	0.3	0.3	0.3
785-122	1,200:5*	C400	0.3	0.3	0.3	0.3	0.3
785-152	1,500:5*	C400	0.3	0.3	0.3	0.3	0.3
785-162	1,600:5*	C400	0.3	0.3	0.3	0.3	0.3
785-202	2,000:5*	C400	0.3	0.3	0.3	0.3	0.3
785-252	2,500:5*	C400	0.3	0.3	0.3	0.3	0.3
785-302	3,000:5*	C400	0.3	0.3	0.3	0.3	0.3
785-402	4,000:5*	C400	0.3	0.3	0.3	0.3	0.3

Approved for revenue metering by Industry Canada No. AE-0657(*)

Model 785



For more information, visit
[gevernova.com/grid-solutions](https://www.gevernova.com/grid-solutions)

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50353
English
251008