

MODEL 3P669

Current Transformer

Window Size 2.87" x 6.30"



Application

3 phase metering.

Frequency

50-400 Hz.

Insulation Level

600 Volts, 10 kV BIL full wave.




Terminals are brass studs No. 8-32 with one flatwasher and regular nut.

Approximate weight 5.5 lbs.

Data Table: Model 3P669

CATALOG NUMBER	CURRENT RATIO	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75°C)
		B0.1	B0.2	B0.5	B0.9	B1.8	
3P669-162	1600:5	0.3	0.3	0.6	1.2	2.4	0.499
3P669-202	2000:5	0.3	0.3	0.3	0.6	1.2	0.624
3P669-242	2400:5	0.3	0.3	0.3	0.6	1.2	0.749
3P669-252	2500:5	0.3	0.3	0.3	0.6	1.2	0.780
3P669-302	3000:5	0.3	0.3	0.3	0.6	0.6	0.936
3P669-322	3200:5	0.3	0.3	0.3	0.3	0.6	1.251
3P669-352	3500:5	0.3	0.3	0.3	0.3	0.6	1.368
3P669-402	4000:5	0.3	0.3	0.3	0.3	0.6	1.952

Model 3P669



For more information, visit
[gevernova.com/grid-solutions](https://www.gevernova.com/grid-solutions)

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50525
 English
 250930