

MODELS JVM-5A

Indoor Voltage Transformer

4,200 V to 14,400 V,
BIL 75 kV to 110 kV, 60 Hz

Application

Designed for indoor service; suitable for operating meters, instruments, relays, and control devices.

Regulatory Agency Approvals

UL RecognizedFile E178265

Thermal Rating (Volt-Amperes)

55 °C Rise above 30 °C Ambient2,000
30 °C Rise above 55 °C Ambient1,400



JVM-5A Voltage Transformer (two-fuse design)

Weight (Approximate in Pounds)

Unfused105/85
Fused110/90

Reference Drawings

Accuracy Curve..... 9932600137
Excitation Curves:
JVM-5A.....9932600139

JVM-5A (two-fuse design)

LINE-TO-LINE CIRCUIT VOLTAGE FOR PERMISSIBLE PRIMARY CONNECTION			TRANSFORMER RATING (1)		ACCURACY CLASSIFICATION 60 Hz		BIL	CATALOG NUMBER	PRIMARY FUSE RATINGS	
			PRIMARY VOLTAGE	RATIO					AMPS	VOLTS
Δ	Y	Y ONLY			ACCUBUTE	ANSI				
Unfused - JVM-5A										
7,200	7,200	12,470	7,200	60:1	0.15 W, X, M, Y	0.3 W, X, M, Y, Z	110 kV	765X023001	---	---
7,620	7,620	13,200	7,620	63.5:1	0.15 W, X, M, Y	0.3 W, X, M, Y, Z	110 kV	765X023002	---	---
8,400	8,400	14,400	8,400	70:1	0.15 W, X, M, Y	0.3 W, X, M, Y, Z	110 kV	765X023003	---	---
12,000	12,000	---	12,000	100:1	0.15 W, X, M, Y	0.3 W, X, M, Y, Z	110 kV	765X023004	---	---
13,200	13,200	---	13,200	110:1	0.15 W, X, M, Y	0.3 W, X, M, Y, Z	110 kV	765X023005	---	---
14,400	14,400	---	14,400	120:1	0.15 W, X, M, Y	0.3 W, X, M, Y, Z	110 kV	765X023006	---	---
One Primary Fuse - JVM5A										
---	---	7,200	7,200 ⁽⁵⁾	60:1	0.15 W, X, M, Y	0.3 W, X, M, Y, Z (2)	110 kV	765X023010	1A	7,200
---	---	12,470	7,200	60:1	0.15 W, X, M, Y	0.3 W, X, M, Y, Z	110 kV	765X023011	1A	14,400
---	---	7,620	7,620	63.5:1	0.15 W, X, M, Y	0.3 W, X, M, Y, Z	110 kV	765X023012	1A	14,400
---	---	8,400	8,400	70:1	0.15 W, X, M, Y	0.3 W, X, M, Y, Z	110 kV	765X023013	1A	14,400
---	---	12,000	12,000	100:1	0.15 W, X, M, Y	0.3 W, X, M, Y, Z (2)	110 kV	765X023014	0.5 A	14,400
---	---	13,200	13,200	110:1	0.15 W, X, M, Y	0.3 W, X, M, Y, Z (2)	110 kV	765X023015	0.5 A	14,400
---	---	14,400	14,400	120:1	0.15 W, X, M, Y	0.3 W, X, M, Y, Z (2)	110 kV	765X023016	0.5 A	14,400
Two Primary Fuses - JVM-5A										
7,200	---	7,200 ⁽⁴⁾	7,200	60:1	0.15 W, X, M, Y	0.3 W, X, M, Y, Z	110 kV	765X023020	1A	7,200
12,000	---	12,000 ⁽⁴⁾	12,000	100:1	0.15 W, X, M, Y	0.3 W, X, M, Y, Z	110 kV	765X023024	0.5 A	14,400
13,200	---	13,200 ⁽⁴⁾	13,200	110:1	0.15 W, X, M, Y	0.3 W, X, M, Y, Z	110 kV	765X023025	0.5 A	14,400
14,400	---	14,400 ⁽⁴⁾	14,400	120:1	0.15 W, X, M, Y	0.3 W, X, M, Y, Z	110 kV	765X023026	0.5 A	14,400

Notes:

(1) For continuous operation, the transformer-rated primary voltage should not be exceeded by more than 10 %.

Under emergency conditions, over-voltage must be limited to 1.25 times the transformer primary voltage rating.

(2) ANSI 69 Volt burden.

(3) This transformer is similar to Catalog Number 764X021011 except for the voltage rating of the fuse.

(4) For Y connections, it is preferred practice to connect one lead from each voltage transformer directly to the grounded neutral, using a fuse only in the line side of the primary. By this connection a transformer can never be "alive" from the line side by reason of a blown fuse on the grounded side.

(5) This transformer is similar to Catalog Number 765X023011 except for the voltage rating of the fuse.

Indoor – Voltage – JVM-5A

Reference Drawings (con't)

Accessories Catalog Number

Fuses, Current-limiting, Type EJ-1:

4,800 Volt Class, 1 Ampere 9F60BDD001

4,800 Volt Class, 2 Ampere 9F60BDD002

7,200 Volt Class, 1 Ampere 9F60BDE001

7,200 Volt Class, 2 Ampere 9F60BDE002

14,400 Volt Class, 0.5 Ampere 9F60BHH905

Construction and Insulation

Please refer to General Product Information, item 1.4.

Core

Please refer to General Product Information, item 2.3.

Primary and Secondary Coils

Please refer to General Product Information, item 3.2.

Primary Terminals

Please refer to General Product Information, item 4.2.

Fuses

Current-limited, Type EJ-1 fuses are used.

Secondary Terminals

Please refer to General Product Information, item 4.12.

Polarity

Please refer to General Product Information, item 7.2.

Baseplate and Mounting

Please refer to General Product Information, item 5.6.

Nameplate

Please refer to General Product Information, item 6.5.

Maintenance

Please refer to General Product Information, item 10.1 and pages 24-27.

For more information, visit
gevernova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50645
English
251014