

MODEL CTWH5-B- 110-T200**

Wound Primary Current Transformer
Medium Voltage



REGULATORY AGENCY APPROVALS



E145172



LR89403

Manufactured to meet the requirements of ANSI/IEEE C57.13.

Application

High accuracy metering and relaying.

Frequency

50-400 Hz

Maximum System Voltage

15.5 kV, BIL 110 kV.

Continuous Thermal Current Rating Factor

5:5 thru 600:5-

1.50 at 30°C., 1.33 at 55°C.

800:5 and over-

1.0 at 30°C., 0.8 at 55°C.

Specifications

Primary terminals are plated copper bars. See chart next page for sizes. Secondary terminals are brass screws No. 10-32 with one flatwasher, lockwasher.

Vacuum cast in polyurethane resin. Other ratios, secondary currents and dual ratios are available. Refer to factory.

Approximate weight 76 lbs.



GE VERNOVA



Model CTWH5-B-110-T200**


CATALOG NUMBER**	CURRENT RATIO	RELAY CLASS	ANSI METERING CLASS AT 60 Hz					*** THERMAL CURRENT RATING 1 SECOND RMS Amps
			B0.1	B0.2	B0.5	B0.9	B1.8	
CTWH5-B-110-T200-050	5:5	T200	0.3	0.3	0.3	0.3	0.3	470
CTWH5-B-110-T200-100	*10:5	T200	0.3	0.3	0.3	0.3	0.3	950
CTWH5-B-110-T200-150	*15:5	T200	0.3	0.3	0.3	0.3	0.3	1440
CTWH5-B-110-T200-200	*20:5	T200	0.3	0.3	0.3	0.3	0.3	1840
CTWH5-B-110-T200-250	*25:5	T200	0.3	0.3	0.3	0.3	0.3	2670
CTWH5-B-110-T200-300	*30:5	T200	0.3	0.3	0.3	0.3	0.3	2920
CTWH5-B-110-T200-400	*40:5	T200	0.3	0.3	0.3	0.3	0.3	3700
CTWH5-B-110-T200-500	*50:5	T200	0.3	0.3	0.3	0.3	0.3	4700
CTWH5-B-110-T200-750	*75:5	T200	0.3	0.3	0.3	0.3	0.3	7575
CTWH5-B-110-T200-101	*100:5	T200	0.3	0.3	0.3	0.3	0.3	12,940
CTWH5-B-110-T200-151	*150:5	T200	0.3	0.3	0.3	0.3	0.3	14,375
CTWH5-B-110-T200-201	*200:5	T200	0.3	0.3	0.3	0.3	0.3	25,875
CTWH5-B-110-T200-301	*300:5	T200	0.3	0.3	0.3	0.3	0.3	27,520
CTWH5-B-110-T200-401	*400:5	T200	0.3	0.3	0.3	0.3	0.3	40,350
CTWH5-B-110-T200-601	*600:5	T200	0.3	0.3	0.3	0.3	0.3	66,225
CTWH5-B-110-T200-801	*800:5	T200	0.3	0.3	0.3	0.3	0.3	66,225
CTWH5-B-110-T200-102	*1,000:5	T200	0.3	0.3	0.3	0.3	0.3	66,225
CTWH5-B-110-T200-122	*1,200:5	T200	0.3	0.3	0.3	0.3	0.3	66,225

* All primary voltages marked with an (*) are approved for revenue metering in Canada by Industry Canada, Approval No. AE-0640 Rev.1.

** Replaces Model CTWH5-110-T200. A test card is provided with each unit.


*** With a burden of 0.35 Ohms or greater connected to the secondary.

Model CTWH5-B-110-T200** Wound Primary CT



Bar Sizes

PRIMARY CURRENT	DIMENSIONS	
	A	B
5 to 200A	0.25	1.50
300 to 600A	0.38	2.00



RECOMMENDED MINIMUM SPACINGS

- A = Unit to Unit = 1.50" minimum.
- B = HV to Ground in Air = 6.50" minimum.

Recommended spacing are for guidance only. User needs to set appropriate values to assure performance for high potential test, impulse test, high humidity, partial discharge, high altitude, and other considerations like configuration.

For more information, visit gevernova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GEA-N50641
English
251014