

MODEL JAU-0C

Indoor Current Transformer

10 kV BIL, 50-800 A
Window Diameter 1.05"/2.06"/3.00"



Model JAU-0C

Application

Designed for indoor service. Suitable for use with indicating instruments and energy management systems. Due to their very low burden capability, these transformers are not normally used with watthour meters for revenue billing.

Regulatory Agency Approvals

UL Recognized FileE93779

Rating Factor

1.0 @ 30°C

Weight

(approximate)

- Transformer with 1.05" window0.5 lbs.
- Transformer with 2.06" window0.6 lbs.
- Transformer with 3.00" window0.9 lbs.

Reference Drawings

- Outlines
- JAU-0C 0121C33701

Insulation Level

0.6 kV; Designed for use with insulated conductors.


Frequency

50-60 Hz

JAU-0C

CURRENT RATIO (Amps) Pri: Sec	OPERATION AT 60 Hz		DIMENSIONS, IN inches (SEE OUTLINE DRAWINGS)			CATALOG NUMBER
	ACCURACY	BURDEN	OUTSIDE Dim. Ax B	WINDOW Dia. C	THICKNESS D	JAU-0C
50:5	3%	1.5 VA @ 1.0 PF	2.47 X 2.74	1.05	1.05	750X191001
60:5	2%	2 VA @ 1.0 PF	2.47 X 2.74	1.05	1.05	750X191002
75:5	2%	2 VA @ 1.0 PF	2.47 X 2.74	1.05	1.05	750X191003
80:5	2%	2 VA @ 1.0 PF	2.47 X 2.74	1.05	1.05	750X191004
100:5	1%	2 VA @ 1.0 PF	2.47 X 2.74	1.05	1.05	750X191005
120:5	1%	2.5 VA @ 0.9 PF	2.47 X 2.74	1.05	1.05	750X191006
125:5	1%	2.5 VA @ 0.9 PF	2.47 X 2.74	1.05	1.05	750X191007
150:5	1%	4 VA @ 0.9 PF	2.47 X 2.74	1.05	1.05	750X191008
200:5	1%	4 VA @ 0.9 PF	2.47 X 2.74	1.05	1.05	750X191010
100:5	1%	1 VA @ 1.0 PF	3.43 X 3.74	2.06	1.10	750X191011
150:5	1%	2.5 VA @ 0.9 PF	3.43 X 3.74	2.06	1.10	750X191012
200:5	1%	4 VA @ 0.9 PF	3.43 X 3.74	2.06	1.10	750X191013
250:5	1%	6 VA @ 0.9 PF	3.43 X 3.74	2.06	1.10	750X191014
300:5	1%	7.5 VA @ 0.9 PF	3.43 X 3.74	2.06	1.10	750X191015
400:5	1%	10 VA @ 0.9 PF	3.43 X 3.74	2.06	1.10	750X191016
500:5	1%	12.5 VA @ 0.9 PF	3.43 X 3.74	2.06	1.10	750X191017
200:5	1%	5 VA @ 0.9 PF	4.50 X 4.88	3.00	1.10	750X191018
250:5	1%	5 VA @ 0.9 PF	4.50 X 4.88	3.00	1.10	750X191019
300:5	1%	6 VA @ 0.9 PF	4.50 X 4.88	3.00	1.10	750X191020
400:5	1%	10 VA @ 0.9 PF	4.50 X 4.88	3.00	1.10	750X191021
500:5	1%	10 VA @ 0.9 PF	4.50 X 4.88	3.00	1.10	750X191022
600:5	1%	10 VA @ 0.9 PF	4.50 X 4.88	3.00	1.10	750X191023
750:5	1%	10 VA @ 0.9 PF	4.50 X 4.88	3.00	1.10	750X191024
800:5	1%	12.5 VA @ 0.9 PF	4.50 X 4.88	3.00	1.10	750X191025

Dimensions - Refer to Data Table



Construction and Insulation

The core and coil are enclosed in a case molded with GE Vernova Noryl thermoplastic PPO resin. This material has excellent electrical and mechanical properties over a wide temperature range, low water absorption and is flame resistant .

Core and Coils

The core is made from high quality grain oriented silicon steel, annealed under rigidly controlled factory conditions. The secondary winding is made of heavy enameled copper wire. The secondary windings are evenly distributed around the core for maximum accuracy and resistance to stray fields from adjacent conductors.

Terminals

Secondary terminals on Model JAU- 0C has 24" flexible leads of #16 stranded wire.

Polarity

The H1 polarity mark is molded into the case, at the side of the window on one face. The X1, X2 polarity marks are also molded into the case adjacent to the secondary terminals. On Model JAU-0C, the polarity X1 lead is white and the non- polarity X2 lead is black.

Primary Conductor

These units are designed to be placed over an insulated cable which forms the primary winding.

Nameplates

The nameplate is a polyester label attached to the side of the transformer.

Mounting

The transformer can be mounted in any position. And, may be suspended from the bus-bar or cable.

Maintenance

These transformers require no maintenance, other than occasional cleaning, if installed where air contamination is severe.

For more information, visit
governova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50517
English
250930