

MODEL 120

Current Transformer

Window Diameter 5.75"



REGULATORY AGENCY APPROVALS
UL E93779 **SP** LR89403
 Manufactured to meet the requirements of ANSI/IEEE C57.13.
 Classified by U.L. in accordance with IEC 44-1

Application

Relaying and metering

Frequency

50-400 Hz.

Insulation Level

600 Volt, 10 kV BIL full wave.

Terminal are brass studs No. 8-32 with one flatwasher, lockwasher and regular nut.

Order mounting bracket kit
 0221B00185 separately.

Multi-ratios available upon request.

Approximate weight 11 lbs.

Model 120

CATALOG NUMBER	CURRENT RATIO	V.A. ±1% CLASS	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75°C)	CONTINUOUS THERMAL RATING FACTOR	
			B0.1	B0.2	B0.5	B0.9	B1.8		@ 30°C	@ 55°C
120-201	200:5	—	1.2	1.2	2.4	4.8	4.8	0.053	2.0	2.0
120-301	300:5 *	C10	0.3	0.6	1.2	2.4	2.4	0.063	2.0	2.0
120-401	400:5*	C10	0.3	0.3	0.6	1.2	2.4	0.080	2.0	2.0
120-501	500:5*	C20	0.3	0.3	0.6	0.6	1.2	0.137	2.0	2.0
120-601	600:5*	C20	0.3	0.3	0.3	0.6	0.6	0.165	2.0	2.0
120-801	800:5*	C20	0.3	0.3	0.3	0.3	0.6	0.220	2.0	1.5
120-102	1,000:5*	C20	0.3	0.3	0.3	0.3	0.6	0.309	1.5	1.5
120-122	1,200:5*	C50	0.3	0.3	0.3	0.3	0.3	0.371	1.5	1.33
120-152	1,500:5*	C50	0.3	0.3	0.3	0.3	0.3	0.464	1.5	1.0
120-162	1,600:5*	C50	0.3	0.3	0.3	0.3	0.3	0.494	1.33	1.0
120-202	2,000:5*	C50	0.3	0.3	0.3	0.3	0.3	0.592	1.33	1.0
120-252	2,500:5*	C50	0.3	0.3	0.3	0.3	0.3	0.740	1.0	0.8
120-302	3,000:5*	C50	0.3	0.3	0.3	0.3	0.3	0.888	1.0	0.8
120-352	3,500:5	C20	0.3	0.3	0.3	0.3	0.3	0.964	1.0	0.8
120-402	4,000:5*	C50	0.3	0.3	0.3	0.3	0.3	1.102	1.0	0.8



Approved for revenue metering by Industry Canada No. T-154



GE VERNOVA



Model 120



For more information, visit
governova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50293
 English
 251010