


MODEL 3P83 AND 3P86

Current Transformer

Window Sizes 1.55" x 0.45", 1.55" x 0.25"



REGULATORY AGENCY APPROVALS
 E93779  LR89403
 Manufactured to meet the requirements of ANSI/IEEE C57.13.
Classified by UL in accordance with IEC 414

Application

3 phase relay, metering and motor overload protection.

Frequency

50-400 Hz.

Insulation Level

600 Volts, 10 kV BIL full wave.

Terminals are brass studs No. 8-32 with one flatwasher, lockwasher and regular nut.

Flexible leads U. L. 1015, 105°C.,
 CSA approved , No. 16 AWG , 24" long
 are available.



Approximate weight 4 lbs.

Model 3P83 and 3P86

CATALOG NUMBER	CURRENT RATIO	V.A FOR 1% CLASS	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75°C)
			B0.1	B0.2	B0.5	B0.9	B1.8	
3P83-500	50:5	2.5	4.8	—	—	—	—	0.015
3P83-101	100:5	2.5	2.4	2.4	4.8	—	—	0.030
3P83-151	150:5	7.5	1.2	1.2	2.4	4.8	4.8	0.045
3P83-201	200:5	10.0	0.6	1.2	2.4	2.4	4.8	0.061
3P83-251	250:5	12.0	0.6	0.6	1.2	2.4	2.4	0.076
3P83-301	300:5	20.0	0.3	0.6	1.2	1.2	2.4	0.091
3P83-401	400:5	25.0	0.3	0.6	0.6	1.2	1.2	0.122
3P83-501	500:5	40.0	0.3	0.3	0.3	0.6	1.2	0.153
3P83-601	600:5	40.0	0.3	0.3	0.6	0.6	0.6	0.161
3P83-801	800:5	60.0	0.3	0.3	0.3	0.3	0.6	0.215

* For Model 3P86 change prefix.

Model 3P83 and 3P86



For more information, visit
[gevernova.com/grid-solutions](https://www.gevernova.com/grid-solutions)

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50526
English
251001