

MODELS 296, 297, 298, 299, 300

Current Transformers

Window Diameter

1.50", 2.25", 3.00", 3.38", 3.75"



Model 296

REGULATORY AGENCY APPROVALS



Manufactured to meet the requirements of ANSI/IEEE C57.13.
Classified by U.L. in accordance with IEC 44-1

Application

Relaying and metering.

Features

50-400 Hz

Insulation Level

600 Volts, 10 kV BIL full wave.

Terminals are brass studs No. 8-32 with one flatwasher, lockwasher and regular nut.

Order mounting bracket kit 0221B00259 separately.

Multi-ratios available on request.


Model 296 Window Diameter 1.50"

Approximate weight 18 lbs.

CATALOG NUMBER	CURRENT RATIO	RELAY CLASS	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75°C)	CONTINUOUS THERMAL RATING FACTOR	
			B0.1	B0.2	B0.5	B0.9	B1.8		@ 30°C	@ 55°C
296-500	50:5	C10	1.2	2.4	4.8	—	—	0.018	2.0	2.0
296-750	75:5	C10	0.6	1.2	2.4	4.8	—	0.027	2.0	2.0
296-101	100:5*	C20	0.6	0.6	1.2	2.4	4.8	0.035	2.0	2.0
296-151	150:5*	C20	0.3	0.3	0.6	1.2	2.4	0.053	2.0	2.0
296-201	200:5*	C20	0.3	0.3	0.6	0.6	1.2	0.071	2.0	2.0
296-251	250:5*	C50	0.3	0.3	0.3	0.3	0.6	0.121	2.0	2.0
296-301	300:5*	C50	0.3	0.3	0.3	0.3	0.6	0.168	2.0	1.5
296-401	400:5*	C100	0.3	0.3	0.3	0.3	0.3	0.224	2.0	1.5
296-501	500:5	C50	0.3	0.3	0.3	0.3	0.3	0.249	1.5	1.5
296-601	600:5	C100	0.3	0.3	0.3	0.3	0.3	0.298	1.5	1.33
296-751	750:5	C100	0.3	0.3	0.3	0.3	0.3	0.373	1.5	1.0
296-801	800:5	C100	0.3	0.3	0.3	0.3	0.3	0.398	1.5	1.0
296-102	1,000:5	C100	0.3	0.3	0.3	0.3	0.3	0.449	1.33	1.0

*Industry Canada Approval No. T-202

EXCITATION CURVE



GE VERNOVA




Model 297 Window Diameter 2.25"

Approximate weight 15 lbs.

CATALOG NUMBER	CURRENT RATIO	RELAY CLASS	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75°C)	CONTINUOUS THERMAL RATING FACTOR	
			B0.1	B0.2	B0.5	B0.9	B1.8		@ 30°C	@ 55°C
297-500	50:5	—	2.4	4.8	—	—	—	0.015	2.0	2.0
297-750	75:5	C10	1.2	2.4	4.8	4.8	—	0.023	2.0	2.0
297-101	100:5	C10	0.6	1.2	2.4	4.8	4.8	0.051	2.0	2.0
297-151	150:5*	C20	0.6	0.6	1.2	2.4	2.4	0.048	2.0	2.0
297-201	200:5*	C20	0.3	0.0	0.6	1.2	2.4	0.103	2.0	2.0
297-251	250:5*	C20	0.3	0.3	0.3	0.6	1.2	0.111	2.0	2.0
297-301	300:5*	C50	0.3	0.3	0.3	0.6	1.2	0.154	2.0	1.5
297-401	400:5*	C50	0.3	0.3	0.3	0.3	0.6	0.205	2.0	1.5
297-501	500:5*	C50	0.3	0.3	0.3	0.3	0.3	0.233	2.0	1.5
297-601	600:5*	C100	0.3	0.3	0.3	0.3	0.3	0.308	1.5	1.33

*Industry Canada Approval No. T-203

EXCITATION CURVE




Model 298 Window Diameter 3.00"

Approximate weight 12 lbs.

CATALOG NUMBER	CURRENT RATIO	RELAY CLASS	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75°C)	CONTINUOUS THERMAL RATING FACTOR	
			B0.1	B0.2	B0.5	B0.9	B1.8		@ 30°C	@ 55°C
298-500	50:5	—	2.4	4.8	—	—	—	0.023	2.0	2.0
298-750	75:5	—	1.2	1.2	4.8	—	—	0.028	2.0	2.0
298-101	100:5	C10	0.6	0.6	2.4	4.8	—	0.040	2.0	2.0
298-151	150:5*	C10	0.6	0.6	1.2	2.4	4.8	0.060	2.0	2.0
298-201	200:5*	C20	0.6	0.6	0.6	1.2	2.4	0.080	2.0	2.0
298-251	250:5*	C20	0.3	0.3	0.6	1.2	2.4	0.073	2.0	2.0
298-301	300:5*	C20	0.3	0.3	0.6	0.6	1.2	0.087	2.0	2.0
298-401	400:5*	C20	0.3	0.3	0.3	0.3	0.6	0.186	2.0	1.5
298-501	500:5*	C50	0.3	0.3	0.3	0.3	0.6	0.233	2.0	1.5
298-601	600:5*	C50	0.3	0.3	0.3	0.3	0.3	0.279	1.5	1.33
298-751	750:5*	C50	0.3	0.3	0.3	0.3	0.3	0.349	1.5	1.0
298-801	800:5*	C50	0.3	0.3	0.3	0.3	0.3	0.372	1.5	1.0

*Industry Canada Approval No. T-204

EXCITATION CURVE



Model 299 Window Diameter 3.38"

Approximate weight 10 lbs.

CATALOG NUMBER	CURRENT RATIO	RELAY CLASS	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75°C)	CONTINUOUS THERMAL RATING FACTOR	
			B0.1	B0.2	B0.5	B0.9	B1.8		@ 30°C	@ 55°C
299-500	50:5	—	4.8	4.8	—	—	—	0.022	2.0	2.0
299-750	75:5	—	1.2	2.4	4.8	—	—	0.028	2.0	2.0
299-101	100:5	—	0.6	1.2	2.4	4.8	—	0.038	2.0	2.0
299-151	150:5*	C10	0.6	0.6	1.2	2.4	4.8	0.057	2.0	2.0
299-201	200:5*	C10	0.6	0.6	1.2	1.2	2.4	0.088	2.0	2.0
299-251	250:5*	C20	0.3	0.3	0.6	1.2	2.4	0.098	2.0	2.0
299-301	300:5*	C20	0.3	0.3	0.3	0.6	1.2	0.118	2.0	2.0
299-401	400:5*	C20	0.3	0.3	0.3	0.6	0.6	0.177	2.0	1.5
299-501	500:5*	C20	0.3	0.3	0.3	0.3	0.6	0.221	2.0	1.5
299-601	600:5*	C50	0.3	0.3	0.3	0.3	0.3	0.265	1.5	1.33
299-751	750:5*	C50	0.3	0.3	0.3	0.3	0.3	0.331	1.5	1.0
299-801	800:5*	C50	0.3	0.3	0.3	0.3	0.3	0.353	1.5	1.0



*Industry Canada Approval No. T-205

Model 300 Window Diameter 3.75"


Approximate weight 9 lbs.

CATALOG NUMBER	CURRENT RATIO	RELAY CLASS	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75°C)	CONTINUOUS THERMAL RATING FACTOR	
			B0.1	B0.2	B0.5	B0.9	B1.8		@ 30°C	@ 55°C
300-500	50:5	—	4.8	—	—	—	—	0.012	2.0	2.0
300-750	75:5	—	2.4	2.4	—	—	—	0.019	2.0	2.0
300-101	100:5	—	2.4	2.4	4.8	—	—	0.026	2.0	2.0
300-151	150:5*	—	0.6	0.6	2.4	2.4	4.8	0.054	2.0	2.0
300-201	200:5*	C10	0.6	0.6	1.2	2.4	4.8	0.072	2.0	2.0
300-251	250:5*	C10	0.3	0.6	1.2	1.2	2.4	0.104	2.0	2.0
300-301	300:5*	C10	0.3	0.3	0.3	0.6	1.2	0.108	2.0	2.0
300-401	400:5*	C20	0.3	0.3	0.3	0.6	1.2	0.144	2.0	1.5
300-501	500:5*	C20	0.3	0.3	0.3	0.6	0.6	0.209	2.0	1.5
300-601	600:5*	C20	0.3	0.3	0.3	0.3	0.6	0.251	1.5	1.33
300-751	750:5*	C20	0.3	0.3	0.3	0.3	0.3	0.329	1.5	1.0
300-801	800:5*	C50	0.3	0.3	0.3	0.3	0.3	0.334	1.5	1.0
300-102	1,000:5*	C50	0.3	0.3	0.3	0.3	0.3	0.418	1.33	1.0
300-122	1,200:5*	C10	0.3	0.3	0.3	0.3	0.3	0.425	1.33	1.0
300-152	1,500:5*	C10	0.3	0.3	0.3	0.3	0.3	0.531	1.0	1.0
300-162	1,600:5*	C10	0.3	0.3	0.3	0.3	0.3	0.567	1.0	0.8
300-202	2,000:5*	C20	0.3	0.3	0.3	0.3	0.3	0.708	1.0	0.8

*Industry Canada Approval No. T-206 Rev. 01



Models 296, 297, 298, 299, 300



For more information, visit
governova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50278
 English
 251010