


MODEL 386MR

Current Transformer Multi-Ratio

Window Diameter 4.50"



REGULATORY AGENCY APPROVALS
UL E93779 **SP** LR89403
Manufactured to meet the requirements of ANSI/IEEE C57.13.
Classified by U.L. in accordance with IEC 44-1

Application

Relaying.

Frequency

50-400 Hz.

Insulation Level



600 Volt, 10 kV BIL full wave.

Terminals are brass screws No. 10-32 with one flatwasher and lockwasher.






Approximate weight 35 lbs.

Model 386MR

CATALOG NUMBER	RELAY CLASS	CONTINUOUS THERMAL RATING FACTOR	
		@ 30°C	@ 55°C
386-601MR	C100	2.0	2.0
386-122MR	C200	2.0	1.5
386-202MR	C200	1.5	1.33
386-302MR	C400	1.5	1.0
386-402MR	C400	1.33	1.0



Model 386MR



For more information, visit
gevernova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GEA-N50780
English
251009