

MODEL 566

Current Transformer

Window Size 2.75" x 2.25"



Application

Metering.

Frequency

50-400 Hz.

Insulation Level

600 Volts, 10 kV BIL full wave.

Continuous Thermal Current Rating Factor

1.33 at 30°C. amb., 1.0 at 55°C. amb.




Terminals are brass studs No. 10-32 with one flatwasher, lockwasher and regular nut.

Approximate weight 2.5 lbs

Model 566

CATALOG NUMBER	CURRENT RATIO	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75°C)
		B0.1	B0.2	B0.5	B0.9	B1.8	
566-201	200:5	1.2	2.4	–	–	–	0,038
566-251	250:5	0.6	1.2	–	–	–	0.030
566-301	300:5	0.6	1.2	2.4	–	–	0.036
566-401	400:5	0.6	1.2	2.4	–	–	0.059
566-501	500:5	0.6	0.6	1.2	2.4	–	0.101

Model 566



For more information, visit
[gevernova.com/grid-solutions](https://www.gevernova.com/grid-solutions)

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50440
 English
 251022