

MODEL 573

Current Transformer

Window Size 3.43" x 5.00"

Application

Metering.

Frequency

50-400 Hz.

Insulation Level

600 Volts, 10 kV BIL full wave.

Model 573

CATALOG NUMBER	CURRENT RATIO	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75°C)
		B0.1	B0.2	B0.5	B0.9	B1.8	
573-401	400:5	0.6	1.2	1.2	2.4	-	0.094
573-501	500:5	0.6	0.6	1.2	1.2	2.4	0.118
573-601	600:5	0.3	0.6	0.6	1.2	2.4	0.141
573-751	750:5	0.3	0.3	0.6	0.6	1.2	0.176
573-801	800:5	0.6	0.3	0.3	0.6	1.2	0.188
573-102	1,000:5	0.3	0.3	0.3	0.6	0.6	0.235
573-122	1,200:5	0.3	0.3	0.3	0.3	0.6	0.282
573-152	1,500:5	0.3	0.3	0.3	0.3	0.6	0.257
573-162	1,600:5	0.3	0.3	0.3	0.3	0.3	0.275
573-202	2,000:5	0.3	0.3	0.3	0.3	0.3	0.383
573-252	2,500:5	0.3	0.3	0.3	0.3	0.3	0.479
573-302	3,000:5	0.3	0.3	0.3	0.3	0.3	0.453
573-322	3,200:5	0.3	0.3	0.3	0.3	0.3	0.483
573-352	3,500:5	0.3	0.3	0.3	0.3	0.3	0.599
573-402	4,000:5	0.3	0.3	0.3	0.3	0.3	0.685



REGULATORY AGENCY APPROVALS
 E93779  LR89403
Manufactured to meet the requirements of ANSI/IEEE C57.13.
Classified by U.L. in accordance with IEC 44-1



Continuous Thermal Current Rating Factor

1.33 at 30°C. amb., 1.0 at 55°C. amb.

Terminals are brass studs No. 10-32 with one flatwasher, lockwasher and regular nut.

Approximate weight 12 lbs.

Model 573



For more information, visit
[gevernova.com/grid-solutions](https://www.gevernova.com/grid-solutions)

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50756
 English
 251009