

MODEL 140MR

Current Transformer Multi-Ratio

Window Diameter 8.13"



REGULATORY AGENCY APPROVALS
 E93779  LR89403
 Manufactured to meet the requirements of ANSI/IEEE C57.13.
 Classified by U.L. in accordance with IEC 44-1

Application

Relaying.

Frequency


50-400 Hz.

Insulation Level


600 Volt, 10 kV BIL full wave.

Model 140MR

CATALOG NUMBER	RELAY CLASS	CONTINUOUS THERMAL RATING FACTOR	
		@ 30°C	@ 55°C
140-601MR	C50	2.0	2.0
140-122MR	C50	1.5	1.5
140-202MR	C100	1.33	1.0
140-302MR	C100	1.0	0.8
140-402MR	C200	1.0	0.8
140-502MR	C50	1.0	0.8









Model 140-601MR



GE VERNOVA



Model 140MR



For more information, visit
gevernova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.