

MODEL 584

Current Transformer

Window Size 2.37" x 3.15"



REGULATORY AGENCY APPROVALS
 E93779  LR89403
Manufactured to meet the requirements of ANSI/IEEE C57.13.
Classified by U.L. in accordance with IEC 44-1

Application

Metering.

Frequency

50-400 Hz.

Insulation Level

600 Volts, 10 kV BIL full wave.

Continuous Thermal Current Rating Factor

1.33 at 30°C. amb., 1.0 at 55°C. amb.


Terminals are brass screws No. 10-32 with one internal tooth lockwasher.

Approximate weight 2 lbs.

Model 584

CATALOG NUMBER	CURRENT RATIO	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75°C)
		B0.1	B0.2	B0.5	B0.9	B1.8	
584-162	1,600:5	0.3	0.3	0.6	0.6	1.2	0.27
584-202	2,000:5	0.3	0.3	0.6	0.6	1.2	0.34
584-252	2,500:5	0.3	0.3	0.6	0.6	0.6	0.48
584-302	3,000:5	0.3	0.3	0.3	0.6	0.6	0.58
584-322	3,200:5	0.3	0.3	0.3	0.6	0.6	0.62

Model 584



For more information, visit
governova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50749
English
251009