

MODEL 593

Current Transformer with Cast Resin Construction

Window Size 8.06"x 22.06"

Application

Relaying.

Frequency

50-400 Hz.

Insulation Level

600 Volts, 10 kV BIL full wave.

Model 593

CATALOG NUMBER	CURRENT RATIO	RELAY CLASS	DEPTH 'A'
593-500	50:5	C10	4.5
593-750	75:5	C20	5.5
593-101	100:5	C30	5.5
593-151	150:5	C50	5.5
593-201	200:5	C50	5.5
593-301	300:5	C100	5.5
593-401	400:5	C100	5.5
593-501	500:5	C200	5.5



REGULATORY AGENCY APPROVALS



E93779

Manufactured to meet the requirements of ANSI/IEEE C57.13.
Classified by U.L. in accordance with IEC 44-1

Continuous Thermal Current Rating Factor

2.0 at 30°C. amb., 2.0 at 55°C. amb.


Terminals are brass screws No. 10-32 with one flatwasher and lockwasher.

Approximate weight 150 lbs.

Excitation data available upon request.



Model 593



For more information, visit
governova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50266
 English
 251010