

MODEL 781MR

Current Transformer with Multi-Ratio

Window Diameter 6.50"

Application

Relaying and Metering.

Frequency

50-400 Hz.

Insulation Level

600 Volts, 10 kV BIL full wave.

Model 781MR

CATALOG NUMBER	RELAY CLASS	ANSI METERING CLASS AT 60 Hz	CONTINUOUS THERMAL RATING FACTOR	
			@ 30°C	@ 55°C
781-601MR	C100	0.3B0.5	2.0	1.5
781-122MR	C200	0.3B1.8	2.0	1.5
781-202MR	C200	0.3B1.8	2.0	1.5
781-302MR	C200	0.3B1.8	1.5	1.33
781-402MR	C200	0.3B1.8	1.0	0.8




REGULATORY AGENCY APPROVALS
UL E93779 **SP** LR89403
Manufactured to meet the requirements of ANSI/IEEE C57.13.
Classified by U.L. in accordance with IEC 44-1

Continuous Thermal Current Rating Factor

Secondary terminals are brass screws No. 10-32 with one flatwasher, lockwasher, accessible from either side.


Approximate weight 30 lbs.

Excitation data available upon request.



CONNECTION DIAGRAM

Model 781MR



For more information, visit
governova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50244
 English
 251010